

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364534

Luminaire Tested: **FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-41)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS ACRYLIC, CLEAR 0.125", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1304.0 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364534

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P364534

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77
5	94	86	81	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71	77	73	70	76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66	74	69	66	72	69	66	64
8	82	73	67	63	80	72	67	63	71	66	63	70	65	62	69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59	66	62	59	66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50487
5°	49462
10°	45660
15°	40589
20°	34641
25°	29024
30°	22747
35°	11991
40°	5602
45°	2206
50°	578
55°	157
60°	104
65°	90
70°	72
75°	95
80°	79
85°	157



TEST NUMBER: P364534

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.9	12.8
10°-20°	398.6	30.6
20°-30°	438.4	33.6
30°-40°	242.0	18.6
40°-50°	51.1	3.9
50°-60°	4.2	0.3
60°-70°	1.3	0.1
70°-80°	1.0	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1004.0	77.0
0°-40°	1246.0	95.6
0°-60°	1301.2	99.8
0°-90°	1304.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1304.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1848	
5°	1804	167
15°	1435	399
25°	963	438
35°	360	242
45°	57	51
55°	3	4
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P364534

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	1848.3
2.5°	1834.3
5°	1803.9
7.5°	1735.1
10°	1646.2
12.5°	1544.3
15°	1435.3
17.5°	1318.4
20°	1191.7
22.5°	1076.6
25°	963.0
27.5°	847.4
30°	721.2
32.5°	549.1
35°	359.6
37.5°	239.0
40°	157.1
42.5°	99.1
45°	57.1
47.5°	29.9
50°	13.6
52.5°	5.6
55°	3.3
57.5°	2.3
60°	1.9
62.5°	1.4
65°	1.4
67.5°	0.9
70°	0.9
72.5°	1.4
75°	0.9
77.5°	0.9
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)