

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364539

Luminaire Tested: **FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BTR84**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364539  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BTR84  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 1500LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1057.9 lumens  
Efficiency: N/A  
Efficacy: 74.5 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364539

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BTR84

### Luminous Intensity Polar Plot





TEST NUMBER: P364539

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BTR84

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	118745
5°	116043
10°	106980
15°	94750
20°	80220
25°	63551
30°	44663
35°	18601
40°	6384
45°	1701
50°	936
55°	874
60°	802
65°	796
70°	775
75°	913
80°	1155
85°	1890



TEST NUMBER: P364539

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BTR84

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.6	14.1
10°-20°	354.6	33.5
20°-30°	364.0	34.4
30°-40°	154.2	14.6
40°-50°	18.9	1.8
50°-60°	6.3	0.6
60°-70°	4.6	0.4
70°-80°	3.6	0.3
80°-90°	2.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	868.2	82.1
0°-40°	1022.4	96.6
0°-60°	1047.6	99.0
0°-90°	1057.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1057.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1658	
5°	1614	150
15°	1278	355
25°	804	364
35°	213	154
45°	17	19
55°	7	6
65°	5	5
75°	3	4
85°	2	2
90°	0	



TEST NUMBER: P364539

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-LI-BTR84

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1658.4
2.5°	1647.7
5°	1614.5
7.5°	1557.4
10°	1471.4
12.5°	1379.7
15°	1278.2
17.5°	1169.2
20°	1052.8
22.5°	928.8
25°	804.4
27.5°	675.8
30°	540.2
32.5°	380.7
35°	212.8
37.5°	122.1
40°	68.3
42.5°	36.0
45°	16.8
47.5°	9.8
50°	8.4
52.5°	7.5
55°	7.0
57.5°	6.5
60°	5.6
62.5°	5.1
65°	4.7
67.5°	4.2
70°	3.7
72.5°	3.7
75°	3.3
77.5°	3.3
80°	2.8
82.5°	2.8
85°	2.3
87.5°	1.4
90°	0.0

(END OF REPORT)