

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365304

Luminaire Tested: **FLD6BX15D010-FEU6B12-8040-F6LBXVM1-MW-BL85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-37)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-MW-BL85
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1156.0 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365304

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-MW-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P365304

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-MW-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	69	89	80	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25592
5°	25026
10°	23734
15°	22247
20°	20758
25°	19093
30°	16357
35°	12451
40°	9146
45°	6930
50°	5673
55°	4991
60°	4458
65°	3910
70°	3338
75°	2607
80°	1746
85°	784



TEST NUMBER: P365304

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-MW-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.3	7.4
10°-20°	220.8	19.1
20°-30°	287.8	24.9
30°-40°	234.6	20.3
40°-50°	142.0	12.3
50°-60°	94.3	8.2
60°-70°	60.3	5.2
70°-80°	26.7	2.3
80°-90°	4.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	593.9	51.4
0°-40°	828.6	71.7
0°-60°	1064.9	92.1
0°-90°	1156.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1156.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	937	
5°	913	85
15°	787	221
25°	634	288
35°	373	235
45°	179	142
55°	105	94
65°	60	60
75°	25	27
85°	2	4
90°	0	



TEST NUMBER: P365304

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-MW-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	936.9
2.5°	929.8
5°	912.7
7.5°	887.0
10°	855.7
12.5°	821.5
15°	786.7
17.5°	751.9
20°	714.1
22.5°	677.8
25°	633.5
27.5°	582.1
30°	518.6
32.5°	446.0
35°	373.4
37.5°	307.9
40°	256.5
42.5°	212.7
45°	179.4
47.5°	153.2
50°	133.5
52.5°	117.4
55°	104.8
57.5°	92.7
60°	81.6
62.5°	71.1
65°	60.5
67.5°	50.9
70°	41.8
72.5°	32.8
75°	24.7
77.5°	17.6
80°	11.1
82.5°	6.0
85°	2.5
87.5°	0.5
90°	0.0

(END OF REPORT)