

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365972

Luminaire Tested: **FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365972
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1156.9 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365972

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P365972

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	84	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40702
5°	40532
10°	38501
15°	34972
20°	30435
25°	25874
30°	20353
35°	11611
40°	5224
45°	2198
50°	693
55°	210
60°	142
65°	116
70°	104
75°	137
80°	63
85°	125



TEST NUMBER: P365972

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.3	12.0
10°-20°	344.0	29.7
20°-30°	389.8	33.7
30°-40°	226.0	19.5
40°-50°	50.1	4.3
50°-60°	5.5	0.5
60°-70°	1.8	0.2
70°-80°	1.1	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	872.1	75.4
0°-40°	1098.1	94.9
0°-60°	1153.7	99.7
0°-90°	1156.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1156.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1490	
5°	1478	138
15°	1237	344
25°	858	390
35°	348	226
45°	57	50
55°	4	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P365972

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BL87

CANDELA DISTRIBUTION (FULL):

0°	
0°	1490.1
2.5°	1491.4
5°	1478.2
7.5°	1446.0
10°	1388.1
12.5°	1318.0
15°	1236.7
17.5°	1151.1
20°	1047.0
22.5°	952.9
25°	858.5
27.5°	757.8
30°	645.3
32.5°	512.4
35°	348.2
37.5°	223.8
40°	146.5
42.5°	95.8
45°	56.9
47.5°	31.8
50°	16.3
52.5°	7.5
55°	4.4
57.5°	3.5
60°	2.6
62.5°	2.2
65°	1.8
67.5°	1.3
70°	1.3
72.5°	1.3
75°	1.3
77.5°	0.9
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)