

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365974

Luminaire Tested: **FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BL89BV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365974  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BL89BV  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS ACRYLIC, CLEAR 0.125", 1500LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1283.0 lumens  
Efficiency: N/A  
Efficacy: 90.3 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365974

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BL89BV

### Luminous Intensity Polar Plot





TEST NUMBER: P365974

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BL89BV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	88	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	78	77
5	94	86	80	76	92	85	79	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	74	71	78	74	70	77	73	70	76	72	69	68
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60
9	77	68	62	59	76	68	62	58	67	62	58	66	61	58	65	61	58	57
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	45595
5°	45292
10°	43067
15°	39079
20°	33902
25°	28819
30°	22678
35°	12775
40°	5737
45°	2387
50°	714
55°	200
60°	126
65°	90
70°	72
75°	95
80°	79
85°	0



TEST NUMBER: P365974

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BL89BV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.3	12.0
10°-20°	383.6	29.9
20°-30°	434.3	33.9
30°-40°	249.0	19.4
40°-50°	54.1	4.2
50°-60°	5.3	0.4
60°-70°	1.6	0.1
70°-80°	0.8	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	972.1	75.8
0°-40°	1221.1	95.2
0°-60°	1280.5	99.8
0°-90°	1283.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1283.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1669	
5°	1652	154
15°	1382	384
25°	956	434
35°	383	249
45°	62	54
55°	4	5
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P365974

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BL89BV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1669.2
2.5°	1664.5
5°	1651.8
7.5°	1608.3
10°	1552.7
12.5°	1473.1
15°	1381.9
17.5°	1277.1
20°	1166.3
22.5°	1062.4
25°	956.2
27.5°	843.9
30°	719.0
32.5°	566.5
35°	383.1
37.5°	242.3
40°	160.9
42.5°	102.9
45°	61.8
47.5°	33.7
50°	16.8
52.5°	7.0
55°	4.2
57.5°	3.3
60°	2.3
62.5°	1.9
65°	1.4
67.5°	1.4
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.5
80°	0.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)