

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365976

Luminaire Tested: **FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BTR80**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365976  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BTR80  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,  
BOTTOM TRIM ACRYLIC, PATTERN 12 0.125", 1500LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1060.0 lumens  
Efficiency: N/A  
Efficacy: 74.6 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365976

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BTR80

### Luminous Intensity Polar Plot





TEST NUMBER: P365976

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BTR80

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	100	92	86	82	97	91	85	81	88	84	80	85	82	79	83	80	77	76
4	94	85	79	74	92	84	78	73	82	77	72	79	75	72	78	74	71	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	79	68	61	57	77	67	61	57	66	60	56	65	60	56	64	59	56	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47
10	67	56	50	46	66	56	50	46	55	49	45	54	49	45	53	49	45	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	75547
5°	73988
10°	69944
15°	63928
20°	56165
25°	47734
30°	39057
35°	30742
40°	22909
45°	16242
50°	11462
55°	8227
60°	5900
65°	4286
70°	3329
75°	2711
80°	2309
85°	2300



TEST NUMBER: P365976

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BTR80

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.1	9.1
10°-20°	240.0	22.6
20°-30°	276.0	26.0
30°-40°	220.3	20.8
40°-50°	127.0	12.0
50°-60°	60.5	5.7
60°-70°	26.2	2.5
70°-80°	10.7	1.0
80°-90°	3.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	612.2	57.7
0°-40°	832.4	78.5
0°-60°	1019.9	96.2
0°-90°	1060.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1060.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1055	
5°	1029	96
15°	862	240
25°	604	276
35°	352	220
45°	160	127
55°	66	61
65°	25	26
75°	10	11
85°	3	3
90°	0	



TEST NUMBER: P365976

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8027-F6LBXVM1-WMH-BTR80

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1055.1
2.5°	1048.5
5°	1029.4
7.5°	1000.8
10°	962.0
12.5°	916.7
15°	862.4
17.5°	803.5
20°	737.1
22.5°	670.2
25°	604.2
27.5°	537.4
30°	472.4
32.5°	413.0
35°	351.7
37.5°	297.0
40°	245.1
42.5°	200.6
45°	160.4
47.5°	128.6
50°	102.9
52.5°	82.3
55°	65.9
57.5°	51.9
60°	41.2
62.5°	32.3
65°	25.3
67.5°	20.1
70°	15.9
72.5°	12.6
75°	9.8
77.5°	7.5
80°	5.6
82.5°	4.2
85°	2.8
87.5°	1.9
90°	0.0

(END OF REPORT)