

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364550

Luminaire Tested: **FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364550
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1224.0 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364550

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P364550

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71	77	73	70	76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66	74	69	66	72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63	70	65	62	69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59	66	62	59	66	62	59	57
10	74	65	60	56	73	65	60	56	64	59	56	63	59	56	63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47092
5°	46197
10°	42662
15°	38015
20°	32466
25°	27267
30°	21404
35°	11091
40°	5299
45°	2086
50°	548
55°	152
60°	98
65°	90
70°	72
75°	95
80°	79
85°	157



TEST NUMBER: P364550

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.2	12.8
10°-20°	373.6	30.5
20°-30°	412.5	33.7
30°-40°	227.0	18.5
40°-50°	48.0	3.9
50°-60°	4.0	0.3
60°-70°	1.2	0.1
70°-80°	0.9	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	942.4	77.0
0°-40°	1169.3	95.5
0°-60°	1221.4	99.8
0°-90°	1224.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1224.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1724	
5°	1685	156
15°	1344	374
25°	905	413
35°	333	227
45°	54	48
55°	3	4
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P364550

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BL87

CANDELA DISTRIBUTION (FULL):

	0°
0°	1724.0
2.5°	1723.1
5°	1684.8
7.5°	1625.8
10°	1538.1
12.5°	1450.9
15°	1344.3
17.5°	1235.9
20°	1116.9
22.5°	1012.6
25°	904.7
27.5°	800.4
30°	678.6
32.5°	518.1
35°	332.6
37.5°	224.2
40°	148.6
42.5°	92.7
45°	54.0
47.5°	27.7
50°	12.9
52.5°	5.5
55°	3.2
57.5°	2.3
60°	1.8
62.5°	1.4
65°	1.4
67.5°	0.9
70°	0.9
72.5°	1.4
75°	0.9
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)