

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364614

Luminaire Tested: **FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BTR87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BTR87
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.375", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1143.0 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364614

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BTR87

Luminous Intensity Polar Plot





TEST NUMBER: P364614

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BTR87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128289
5°	125365
10°	115574
15°	102363
20°	86667
25°	68662
30°	48251
35°	20095
40°	6898
45°	1843
50°	1014
55°	949
60°	874
65°	864
70°	837
75°	968
80°	1237
85°	2054



TEST NUMBER: P364614

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BTR87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.6	14.1
10°-20°	383.1	33.5
20°-30°	393.3	34.4
30°-40°	166.5	14.6
40°-50°	20.5	1.8
50°-60°	6.8	0.6
60°-70°	5.0	0.4
70°-80°	3.8	0.3
80°-90°	2.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	938.0	82.1
0°-40°	1104.6	96.6
0°-60°	1131.8	99.0
0°-90°	1143.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1143.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1792	
5°	1744	162
15°	1381	383
25°	869	393
35°	230	167
45°	18	20
55°	8	7
65°	5	5
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P364614

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BTR87

CANDELA DISTRIBUTION (FULL):

0°	
0°	1791.7
2.5°	1780.1
5°	1744.2
7.5°	1682.5
10°	1589.6
12.5°	1490.5
15°	1380.9
17.5°	1263.2
20°	1137.4
22.5°	1003.5
25°	869.1
27.5°	730.1
30°	583.6
32.5°	411.3
35°	229.9
37.5°	131.9
40°	73.8
42.5°	38.9
45°	18.2
47.5°	10.6
50°	9.1
52.5°	8.1
55°	7.6
57.5°	7.1
60°	6.1
62.5°	5.6
65°	5.1
67.5°	4.5
70°	4.0
72.5°	4.0
75°	3.5
77.5°	3.5
80°	3.0
82.5°	3.0
85°	2.5
87.5°	1.5
90°	0.0

(END OF REPORT)