

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364556

Luminaire Tested: **FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR82**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364556  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR82  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.187", 1500LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1068.1 lumens  
Efficiency: N/A  
Efficacy: 75.2 lumens/watt  
Spacing Criteria (0/90/45): 1.07 / 1.07 / 1.07  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364556

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR82

### Luminous Intensity Polar Plot





TEST NUMBER: P364556

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR82

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	83	76	71	90	81	75	70	79	74	69	77	72	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60
6	81	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	43	42
10	63	52	45	41	62	52	45	41	51	45	41	50	44	40	49	44	40	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	51747
5°	51801
10°	52363
15°	51904
20°	49734
25°	45814
30°	40546
35°	34579
40°	28247
45°	22085
50°	16286
55°	11297
60°	7217
65°	4388
70°	2973
75°	2296
80°	2020
85°	2793



TEST NUMBER: P364556

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR82

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.8	6.4
10°-20°	195.8	18.3
20°-30°	264.8	24.8
30°-40°	246.4	23.1
40°-50°	168.8	15.8
50°-60°	83.2	7.8
60°-70°	27.8	2.6
70°-80°	9.2	0.9
80°-90°	3.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.5	49.6
0°-40°	775.8	72.6
0°-60°	1027.8	96.2
0°-90°	1068.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1068.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	723	
5°	721	69
15°	700	196
25°	580	265
35°	396	246
45°	218	169
55°	90	83
65°	26	28
75°	8	9
85°	3	3
90°	0	



TEST NUMBER: P364556

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR82

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	722.7
2.5°	721.7
5°	720.7
7.5°	721.7
10°	720.2
12.5°	712.4
15°	700.2
17.5°	677.7
20°	652.7
22.5°	619.5
25°	579.9
27.5°	536.9
30°	490.4
32.5°	444.0
35°	395.6
37.5°	347.6
40°	302.2
42.5°	258.2
45°	218.1
47.5°	179.9
50°	146.2
52.5°	116.9
55°	90.5
57.5°	68.9
60°	50.4
62.5°	36.2
65°	25.9
67.5°	18.6
70°	14.2
72.5°	10.8
75°	8.3
77.5°	6.4
80°	4.9
82.5°	3.9
85°	3.4
87.5°	2.0
90°	0.0

(END OF REPORT)