

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364557

Luminaire Tested: **FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364557
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR84
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1106.0 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364557

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR84

Luminous Intensity Polar Plot





TEST NUMBER: P364557

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	124136
5°	121304
10°	111830
15°	99049
20°	83855
25°	66434
30°	46689
35°	19449
40°	6674
45°	1782
50°	980
55°	911
60°	845
65°	830
70°	816
75°	941
80°	1196
85°	1972



TEST NUMBER: P364557

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.4	14.1
10°-20°	370.7	33.5
20°-30°	380.5	34.4
30°-40°	161.2	14.6
40°-50°	19.8	1.8
50°-60°	6.5	0.6
60°-70°	4.9	0.4
70°-80°	3.7	0.3
80°-90°	2.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	907.6	82.1
0°-40°	1068.8	96.6
0°-60°	1095.1	99.0
0°-90°	1106.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1106.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1734	
5°	1688	156
15°	1336	371
25°	841	381
35°	222	161
45°	18	20
55°	7	7
65°	5	5
75°	3	4
85°	2	2
90°	0	



TEST NUMBER: P364557

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8030-F6LBXVM1-LI-BTR84

CANDELA DISTRIBUTION (FULL):

	0°
0°	1733.7
2.5°	1722.4
5°	1687.7
7.5°	1628.1
10°	1538.1
12.5°	1442.3
15°	1336.2
17.5°	1222.3
20°	1100.5
22.5°	971.0
25°	840.9
27.5°	706.5
30°	564.7
32.5°	398.0
35°	222.5
37.5°	127.6
40°	71.4
42.5°	37.6
45°	17.6
47.5°	10.3
50°	8.8
52.5°	7.8
55°	7.3
57.5°	6.8
60°	5.9
62.5°	5.4
65°	4.9
67.5°	4.4
70°	3.9
72.5°	3.9
75°	3.4
77.5°	3.4
80°	2.9
82.5°	2.9
85°	2.4
87.5°	1.5
90°	0.0

(END OF REPORT)