

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364624

Luminaire Tested: **FLD6BX20D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364624  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,  
BOTTOM LENS ACRYLIC, CLEAR 0.125", 2000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1794.0 lumens  
Efficiency: N/A  
Efficacy: 88.4 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364624

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV

### Luminous Intensity Polar Plot





TEST NUMBER: P364624

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	81	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	73	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	59	56	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	69457
5°	68047
10°	62821
15°	55842
20°	47655
25°	39928
30°	31295
35°	16499
40°	7709
45°	3032
50°	795
55°	214
60°	142
65°	123
70°	104
75°	137
80°	94
85°	188



TEST NUMBER: P364624

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	229.7	12.8
10°-20°	548.4	30.6
20°-30°	603.2	33.6
30°-40°	333.0	18.6
40°-50°	70.3	3.9
50°-60°	5.7	0.3
60°-70°	1.7	0.1
70°-80°	1.4	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1381.2	77.0
0°-40°	1714.2	95.6
0°-60°	1790.2	99.8
0°-90°	1794.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1794.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2543	
5°	2482	230
15°	1975	548
25°	1325	603
35°	495	333
45°	78	70
55°	4	6
65°	2	2
75°	1	1
85°	1	1
90°	0	



TEST NUMBER: P364624

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-LI-BL89BV

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2542.8
2.5°	2523.5
5°	2481.7
7.5°	2387.1
10°	2264.9
12.5°	2124.6
15°	1974.7
17.5°	1813.8
20°	1639.4
22.5°	1481.2
25°	1324.8
27.5°	1165.9
30°	992.2
32.5°	755.4
35°	494.8
37.5°	328.8
40°	216.2
42.5°	136.4
45°	78.5
47.5°	41.2
50°	18.7
52.5°	7.7
55°	4.5
57.5°	3.2
60°	2.6
62.5°	1.9
65°	1.9
67.5°	1.3
70°	1.3
72.5°	1.9
75°	1.3
77.5°	1.3
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)