

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364636

Luminaire Tested: **FLD6BX20D010-FEU6B12-8027-F6LBXVM1-LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364636
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-LI
Description: VANDAL RESISTANT OPEN, SPECULAR CLEAR REFLECTOR, 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1886.0 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364636

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-LI

Luminous Intensity Polar Plot





TEST NUMBER: P364636

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	88	84	81	87	83	80	85	82	79	78
5	94	86	81	77	93	85	80	77	84	79	76	82	78	75	81	77	75	73
6	90	81	76	72	88	81	75	72	79	75	71	78	74	71	77	73	70	69
7	86	77	71	67	84	76	71	67	75	70	67	74	70	66	73	69	66	65
8	82	73	67	63	81	72	67	63	71	66	63	70	66	63	69	65	62	61
9	78	69	64	60	77	69	63	60	68	63	60	67	62	59	66	62	59	58
10	75	66	60	57	74	65	60	57	64	60	56	64	59	56	63	59	56	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74472
5°	72763
10°	67267
15°	59485
20°	50710
25°	42183
30°	32717
35°	16993
40°	7895
45°	2982
50°	654
55°	90
60°	33
65°	39
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P364636

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.9	13.0
10°-20°	584.7	31.0
20°-30°	637.3	33.8
30°-40°	344.6	18.3
40°-50°	69.6	3.7
50°-60°	3.3	0.2
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1468.0	77.8
0°-40°	1812.5	96.1
0°-60°	1885.4	100.0
0°-90°	1886.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1886.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2726	
5°	2654	246
15°	2104	585
25°	1400	637
35°	510	345
45°	77	70
55°	2	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P364636

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2726.4
2.5°	2708.4
5°	2653.7
7.5°	2555.2
10°	2425.2
12.5°	2270.2
15°	2103.5
17.5°	1931.1
20°	1744.5
22.5°	1568.8
25°	1399.6
27.5°	1229.7
30°	1037.3
32.5°	780.5
35°	509.6
37.5°	340.4
40°	221.4
42.5°	136.4
45°	77.2
47.5°	38.6
50°	15.4
52.5°	3.9
55°	1.9
57.5°	1.3
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)