

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364575

Luminaire Tested: **FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR84**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364575  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR84  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 1500LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1128.1 lumens  
Efficiency: N/A  
Efficacy: 79.4 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364575

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR84

### Luminous Intensity Polar Plot





TEST NUMBER: P364575

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR84

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	126606
5°	123719
10°	114055
15°	101021
20°	85524
25°	67762
30°	47615
35°	19833
40°	6805
45°	1823
50°	1003
55°	936
60°	859
65°	847
70°	837
75°	968
80°	1237
85°	2054



TEST NUMBER: P364575

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR84

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.5	14.1
10°-20°	378.1	33.5
20°-30°	388.1	34.4
30°-40°	164.3	14.6
40°-50°	20.2	1.8
50°-60°	6.7	0.6
60°-70°	5.0	0.4
70°-80°	3.8	0.3
80°-90°	2.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	925.7	82.1
0°-40°	1090.0	96.6
0°-60°	1117.0	99.0
0°-90°	1128.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1128.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1768	
5°	1721	160
15°	1363	378
25°	858	388
35°	227	164
45°	18	20
55°	8	7
65°	5	5
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P364575

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8035-F6LBXVM1-LI-BTR84

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1768.2
2.5°	1756.7
5°	1721.3
7.5°	1660.5
10°	1568.7
12.5°	1471.0
15°	1362.8
17.5°	1246.6
20°	1122.4
22.5°	990.3
25°	857.7
27.5°	720.5
30°	575.9
32.5°	405.9
35°	226.9
37.5°	130.1
40°	72.8
42.5°	38.4
45°	18.0
47.5°	10.5
50°	9.0
52.5°	8.0
55°	7.5
57.5°	7.0
60°	6.0
62.5°	5.5
65°	5.0
67.5°	4.5
70°	4.0
72.5°	4.0
75°	3.5
77.5°	3.5
80°	3.0
82.5°	3.0
85°	2.5
87.5°	1.5
90°	0.0

(END OF REPORT)