

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366063

Luminaire Tested: **FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BL89AM**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366063  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-48)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BL89AM  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, OPAL SMOOTH 0.125", 2000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 718.0 lumens  
Efficiency: N/A  
Efficacy: 35.4 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.38  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366063

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BL89AM

### Luminous Intensity Polar Plot





TEST NUMBER: P366063

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BL89AM

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92		94	91	89		90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	75		82	78	74		79	75	72	70
3	90	80	71	65	88	78	70	64	75	69	63		72	67	62		70	65	61	59
4	83	70	62	55	80	69	61	55	67	59	54		64	58	53		62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	46		58	51	46		56	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41		52	45	40		51	45	40	38
7	65	51	42	36	63	50	42	36	49	41	36		47	41	36		46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32		43	37	32		42	36	32	30
9	56	43	35	29	55	42	34	29	41	34	29		40	33	29		39	33	29	27
10	53	40	32	26	52	39	31	26	38	31	26		37	31	26		36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	6911
5°	6921
10°	6893
15°	6846
20°	6811
25°	6772
30°	6721
35°	6656
40°	6611
45°	6540
50°	6429
55°	6315
60°	6119
65°	5869
70°	5447
75°	4823
80°	3854
85°	2225



TEST NUMBER: P366063

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BL89AM

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	24.0	3.3
10°-20°	68.5	9.5
20°-30°	103.6	14.4
30°-40°	125.1	17.4
40°-50°	130.5	18.2
50°-60°	118.3	16.5
60°-70°	89.7	12.5
70°-80°	48.5	6.8
80°-90°	10.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.0	27.3
0°-40°	321.1	44.7
0°-60°	569.8	79.4
0°-90°	718.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	718.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	253	
5°	252	24
15°	242	68
25°	225	104
35°	200	125
45°	169	130
55°	133	118
65°	91	90
75°	46	49
85°	7	10
90°	0	



TEST NUMBER: P366063

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BL89AM

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	253.0
2.5°	252.4
5°	252.4
7.5°	251.1
10°	248.5
12.5°	245.9
15°	242.1
17.5°	239.5
20°	234.3
22.5°	229.8
25°	224.7
27.5°	219.5
30°	213.1
32.5°	207.3
35°	199.6
37.5°	192.5
40°	185.4
42.5°	177.7
45°	169.3
47.5°	160.3
50°	151.3
52.5°	142.3
55°	132.6
57.5°	122.3
60°	112.0
62.5°	101.7
65°	90.8
67.5°	79.8
70°	68.2
72.5°	57.3
75°	45.7
77.5°	34.8
80°	24.5
82.5°	15.5
85°	7.1
87.5°	1.9
90°	0.0

(END OF REPORT)