

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366069

Luminaire Tested: **FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BTR84**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366069  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BTR84  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,  
BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 2000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1432.9 lumens  
Efficiency: N/A  
Efficacy: 70.6 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366069

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BTR84

### Luminous Intensity Polar Plot





TEST NUMBER: P366069

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BTR84

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	148159
5°	145720
10°	138847
15°	126877
20°	108802
25°	87299
30°	61207
35°	28277
40°	9076
45°	2926
50°	1359
55°	1198
60°	1203
65°	1084
70°	1068
75°	1245
80°	1608
85°	2629



TEST NUMBER: P366069

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BTR84

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	190.1	13.3
10°-20°	473.6	33.1
20°-30°	497.4	34.7
30°-40°	220.7	15.4
40°-50°	28.5	2.0
50°-60°	8.9	0.6
60°-70°	6.3	0.4
70°-80°	4.6	0.3
80°-90°	2.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1161.2	81.0
0°-40°	1381.9	96.4
0°-60°	1419.3	99.0
0°-90°	1432.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1432.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2069	
5°	2027	190
15°	1712	474
25°	1105	497
35°	324	221
45°	29	29
55°	10	9
65°	6	6
75°	4	5
85°	3	3
90°	0	



TEST NUMBER: P366069

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BTR84

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2069.2
2.5°	2056.3
5°	2027.4
7.5°	1988.1
10°	1909.7
12.5°	1821.5
15°	1711.6
17.5°	1579.7
20°	1427.9
22.5°	1268.4
25°	1105.0
27.5°	921.7
30°	740.3
32.5°	544.1
35°	323.5
37.5°	172.4
40°	97.1
42.5°	53.4
45°	28.9
47.5°	14.8
50°	12.2
52.5°	10.9
55°	9.6
57.5°	9.0
60°	8.4
62.5°	7.1
65°	6.4
67.5°	5.1
70°	5.1
72.5°	4.5
75°	4.5
77.5°	3.9
80°	3.9
82.5°	3.2
85°	3.2
87.5°	1.9
90°	0.0

(END OF REPORT)