

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364593

Luminaire Tested: **FLD6BX15D010-FEU6B12-8040-F6LBXVM1-LI-BTR84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-LI-BTR84
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1139.9 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364593

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-LI-BTR84

Luminous Intensity Polar Plot





TEST NUMBER: P364593

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-LI-BTR84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127953
5°	125034
10°	115269
15°	102096
20°	86438
25°	68481
30°	48127
35°	20043
40°	6879
45°	1833
50°	1014
55°	949
60°	859
65°	847
70°	837
75°	968
80°	1237
85°	2054



TEST NUMBER: P364593

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-LI-BTR84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.2	14.1
10°-20°	382.1	33.5
20°-30°	392.2	34.4
30°-40°	166.1	14.6
40°-50°	20.4	1.8
50°-60°	6.8	0.6
60°-70°	5.0	0.4
70°-80°	3.8	0.3
80°-90°	2.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.5	82.1
0°-40°	1101.6	96.6
0°-60°	1128.9	99.0
0°-90°	1139.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1139.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1787	
5°	1740	161
15°	1377	382
25°	867	392
35°	229	166
45°	18	20
55°	8	7
65°	5	5
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P364593

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-LI-BTR84

CANDELA DISTRIBUTION (FULL):

0°	
0°	1787.0
2.5°	1775.4
5°	1739.6
7.5°	1678.1
10°	1585.4
12.5°	1486.6
15°	1377.3
17.5°	1259.9
20°	1134.4
22.5°	1000.8
25°	866.8
27.5°	728.2
30°	582.1
32.5°	410.2
35°	229.3
37.5°	131.5
40°	73.6
42.5°	38.8
45°	18.1
47.5°	10.6
50°	9.1
52.5°	8.1
55°	7.6
57.5°	7.1
60°	6.0
62.5°	5.5
65°	5.0
67.5°	4.5
70°	4.0
72.5°	4.0
75°	3.5
77.5°	3.5
80°	3.0
82.5°	3.0
85°	2.5
87.5°	1.5
90°	0.0

(END OF REPORT)