

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366074

Luminaire Tested: **FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BTR89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BTR89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM ACRYLIC, CLEAR 0.125", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1496.0 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366074

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BTR89BV

Luminous Intensity Polar Plot





TEST NUMBER: P366074

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BTR89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	154961
5°	152872
10°	145515
15°	132281
20°	113907
25°	91060
30°	63844
35°	29702
40°	9384
45°	2937
50°	1292
55°	1211
60°	1103
65°	983
70°	1068
75°	1245
80°	1608
85°	2629



TEST NUMBER: P366074

CATALOG NUMBER: FLD6BX20D010-FEUG6B12-8027-F6LBXVM1-WMH-BTR89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.1	13.3
10°-20°	494.8	33.1
20°-30°	520.2	34.8
30°-40°	230.8	15.4
40°-50°	28.9	1.9
50°-60°	8.6	0.6
60°-70°	6.0	0.4
70°-80°	4.8	0.3
80°-90°	2.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1214.1	81.2
0°-40°	1444.9	96.6
0°-60°	1482.4	99.1
0°-90°	1496.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1496.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2164	
5°	2127	199
15°	1784	495
25°	1153	520
35°	340	231
45°	29	29
55°	10	9
65°	6	6
75°	4	5
85°	3	3
90°	0	



TEST NUMBER: P366074

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BTR89BV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2164.2
2.5°	2150.0
5°	2126.9
7.5°	2079.3
10°	2001.4
12.5°	1906.1
15°	1784.5
17.5°	1647.4
20°	1494.9
22.5°	1329.5
25°	1152.6
27.5°	964.7
30°	772.2
32.5°	568.2
35°	339.8
37.5°	180.8
40°	100.4
42.5°	54.7
45°	29.0
47.5°	14.2
50°	11.6
52.5°	10.3
55°	9.7
57.5°	9.0
60°	7.7
62.5°	7.1
65°	5.8
67.5°	5.1
70°	5.1
72.5°	4.5
75°	4.5
77.5°	4.5
80°	3.9
82.5°	3.2
85°	3.2
87.5°	1.9
90°	0.0

(END OF REPORT)