

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366024

Luminaire Tested: **FLD6BX15D010-FEU6B12-8040-F6LBXVM1-WMH-BL85**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366024  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-WMH-BL85  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 1500LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1316.0 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366024

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-WMH-BL85

### Luminous Intensity Polar Plot





TEST NUMBER: P366024

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-WMH-BL85

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	46297
5°	46101
10°	43793
15°	39780
20°	34615
25°	29431
30°	23151
35°	13208
40°	5944
45°	2503
50°	790
55°	238
60°	164
65°	129
70°	120
75°	158
80°	79
85°	157



TEST NUMBER: P366024

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-WMH-BL85

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.3	12.0
10°-20°	391.3	29.7
20°-30°	443.4	33.7
30°-40°	257.1	19.5
40°-50°	57.0	4.3
50°-60°	6.2	0.5
60°-70°	2.0	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	992.0	75.4
0°-40°	1249.0	94.9
0°-60°	1312.3	99.7
0°-90°	1316.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1316.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1695	
5°	1681	157
15°	1407	391
25°	976	443
35°	396	257
45°	65	57
55°	5	6
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P366024

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-WMH-BL85

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1694.9
2.5°	1696.4
5°	1681.3
7.5°	1644.7
10°	1578.9
12.5°	1499.1
15°	1406.7
17.5°	1309.3
20°	1190.8
22.5°	1083.9
25°	976.5
27.5°	862.0
30°	734.0
32.5°	582.9
35°	396.1
37.5°	254.5
40°	166.7
42.5°	108.9
45°	64.8
47.5°	36.1
50°	18.6
52.5°	8.5
55°	5.0
57.5°	4.0
60°	3.0
62.5°	2.5
65°	2.0
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	1.0
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)