

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364650

Luminaire Tested: **FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR87**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364650  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR87  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.375", 2000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1490.0 lumens  
Efficiency: N/A  
Efficacy: 73.4 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364650

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR87

### Luminous Intensity Polar Plot





TEST NUMBER: P364650

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR87

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	167233
5°	163423
10°	150655
15°	133437
20°	112970
25°	89504
30°	62902
35°	26197
40°	8992
45°	2400
50°	1326
55°	1236
60°	1131
65°	1118
70°	1110
75°	1273
80°	1649
85°	2711



TEST NUMBER: P364650

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR87

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	210.7	14.1
10°-20°	499.4	33.5
20°-30°	512.7	34.4
30°-40°	217.1	14.6
40°-50°	26.7	1.8
50°-60°	8.8	0.6
60°-70°	6.5	0.4
70°-80°	5.1	0.3
80°-90°	3.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1222.8	82.1
0°-40°	1439.8	96.6
0°-60°	1475.4	99.0
0°-90°	1490.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1490.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2336	
5°	2274	211
15°	1800	499
25°	1133	513
35°	300	217
45°	24	27
55°	10	9
65°	7	7
75°	5	5
85°	3	3
90°	0	



TEST NUMBER: P364650

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR87

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2335.6
2.5°	2320.5
5°	2273.7
7.5°	2193.3
10°	2072.1
12.5°	1943.0
15°	1800.1
17.5°	1646.6
20°	1482.6
22.5°	1308.1
25°	1132.9
27.5°	951.8
30°	760.8
32.5°	536.1
35°	299.7
37.5°	171.9
40°	96.2
42.5°	50.7
45°	23.7
47.5°	13.8
50°	11.9
52.5°	10.5
55°	9.9
57.5°	9.2
60°	7.9
62.5°	7.2
65°	6.6
67.5°	5.9
70°	5.3
72.5°	5.3
75°	4.6
77.5°	4.6
80°	4.0
82.5°	4.0
85°	3.3
87.5°	2.0
90°	0.0

(END OF REPORT)