

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366037

Luminaire Tested: **FLD6BX15D010-FEU6B12-8040-F6LBXVM1-WMH-BTR89BI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366037
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-WMH-BTR89BI
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1083.0 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366037

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-WMH-BTR89BI

Luminous Intensity Polar Plot





TEST NUMBER: P366037

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-WMH-BTR89BI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112179
5°	110666
10°	105344
15°	95766
20°	82461
25°	65921
30°	46217
35°	21503
40°	6795
45°	2126
50°	936
55°	874
60°	802
65°	712
70°	775
75°	913
80°	1155
85°	1890



TEST NUMBER: P366037

CATALOG NUMBER: FLD6BX15D010-FEUG6B12-8040-F6LBXVM1-WMH-BTR89BI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.1	13.3
10°-20°	358.2	33.1
20°-30°	376.6	34.8
30°-40°	167.1	15.4
40°-50°	20.9	1.9
50°-60°	6.3	0.6
60°-70°	4.4	0.4
70°-80°	3.5	0.3
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	878.9	81.2
0°-40°	1046.0	96.6
0°-60°	1073.1	99.1
0°-90°	1083.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1083.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1567	
5°	1540	144
15°	1292	358
25°	834	377
35°	246	167
45°	21	21
55°	7	6
65°	4	4
75°	3	3
85°	2	2
90°	0	



TEST NUMBER: P366037

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8040-F6LBXVM1-WMH-BTR89BI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1566.7
2.5°	1556.5
5°	1539.7
7.5°	1505.2
10°	1448.9
12.5°	1379.9
15°	1291.9
17.5°	1192.6
20°	1082.2
22.5°	962.5
25°	834.4
27.5°	698.3
30°	559.0
32.5°	411.4
35°	246.0
37.5°	130.9
40°	72.7
42.5°	39.6
45°	21.0
47.5°	10.2
50°	8.4
52.5°	7.5
55°	7.0
57.5°	6.5
60°	5.6
62.5°	5.1
65°	4.2
67.5°	3.7
70°	3.7
72.5°	3.3
75°	3.3
77.5°	3.3
80°	2.8
82.5°	2.3
85°	2.3
87.5°	1.4
90°	0.0

(END OF REPORT)