

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364653

Luminaire Tested: **FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR94**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364653
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-27)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR94
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM GLASS, TEMPERED CLEAR 0.187", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1554.0 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364653

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR94

Luminous Intensity Polar Plot





TEST NUMBER: P364653

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR94

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	88
3	104	98	93	90	102	96	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		77	74	71	70
7	87	78	73	69	85	77	72	68	76	72	68		75	71	68		74	70	67	66
8	83	74	69	65	82	74	68	65	73	68	64		72	67	64		71	67	64	63
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		67	64	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	173942
5°	169338
10°	156530
15°	139345
20°	117359
25°	93517
30°	65506
35°	27744
40°	9683
45°	2653
50°	1348
55°	1261
60°	1246
65°	1135
70°	1130
75°	1494
80°	1938
85°	2793



TEST NUMBER: P364653

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR94

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.4	14.1
10°-20°	519.7	33.4
20°-30°	534.6	34.4
30°-40°	228.3	14.7
40°-50°	28.5	1.8
50°-60°	9.1	0.6
60°-70°	6.7	0.4
70°-80°	5.4	0.3
80°-90°	3.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1272.7	81.9
0°-40°	1501.0	96.6
0°-60°	1538.6	99.0
0°-90°	1554.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1554.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2429	
5°	2356	218
15°	1880	520
25°	1184	535
35°	317	228
45°	26	28
55°	10	9
65°	7	7
75°	5	5
85°	3	3
90°	0	



TEST NUMBER: P364653

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR94

CANDELA DISTRIBUTION (FULL):

	0°
0°	2429.3
2.5°	2409.8
5°	2356.0
7.5°	2269.9
10°	2152.9
12.5°	2022.4
15°	1879.8
17.5°	1710.3
20°	1540.2
22.5°	1365.3
25°	1183.7
27.5°	992.0
30°	792.3
32.5°	562.9
35°	317.4
37.5°	181.6
40°	103.6
42.5°	53.8
45°	26.2
47.5°	14.1
50°	12.1
52.5°	10.8
55°	10.1
57.5°	9.4
60°	8.7
62.5°	7.4
65°	6.7
67.5°	6.1
70°	5.4
72.5°	5.4
75°	5.4
77.5°	4.7
80°	4.7
82.5°	4.0
85°	3.4
87.5°	2.0
90°	0.0

(END OF REPORT)