

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365361

Luminaire Tested: **FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BL89AM**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365361
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-40)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BL89AM
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, OPAL SMOOTH 0.125", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 683.1 lumens
Efficiency: N/A
Efficacy: 33.6 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365361

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P365361

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92		94	91	89		90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	75		82	78	74		79	75	72	70
3	90	80	71	65	88	78	70	64	75	69	63		72	67	62		70	65	61	59
4	82	70	62	55	80	69	61	55	67	59	54		64	58	53		62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	46		58	51	46		56	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41		52	45	40		51	45	40	38
7	65	51	42	36	63	50	42	36	49	41	36		47	41	36		46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32		43	37	32		42	36	32	30
9	56	43	35	29	55	42	34	29	41	34	29		40	33	29		39	33	29	27
10	53	40	32	26	52	39	31	26	38	31	26		37	31	26		36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6564
5°	6589
10°	6554
15°	6530
20°	6497
25°	6432
30°	6390
35°	6352
40°	6265
45°	6188
50°	6119
55°	6024
60°	5813
65°	5571
70°	5215
75°	4623
80°	3712
85°	2100



TEST NUMBER: P365361

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.8	3.3
10°-20°	65.1	9.5
20°-30°	98.5	14.4
30°-40°	118.9	17.4
40°-50°	123.8	18.1
50°-60°	112.6	16.5
60°-70°	85.2	12.5
70°-80°	46.5	6.8
80°-90°	9.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	186.4	27.3
0°-40°	305.3	44.7
0°-60°	541.7	79.3
0°-90°	683.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	683.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	240	
5°	240	23
15°	231	65
25°	213	99
35°	190	119
45°	160	124
55°	126	113
65°	86	85
75°	44	47
85°	7	10
90°	0	



TEST NUMBER: P365361

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BL89AM

CANDELA DISTRIBUTION (FULL):

0°	
0°	240.3
2.5°	241.0
5°	240.3
7.5°	238.3
10°	236.3
12.5°	233.6
15°	230.9
17.5°	226.8
20°	223.5
22.5°	218.8
25°	213.4
27.5°	208.7
30°	202.6
32.5°	196.6
35°	190.5
37.5°	183.1
40°	175.7
42.5°	168.3
45°	160.2
47.5°	152.8
50°	144.0
52.5°	135.3
55°	126.5
57.5°	116.4
60°	106.4
62.5°	96.3
65°	86.2
67.5°	76.1
70°	65.3
72.5°	54.5
75°	43.8
77.5°	33.7
80°	23.6
82.5°	14.8
85°	6.7
87.5°	2.0
90°	0.0

(END OF REPORT)