

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364603

Luminaire Tested: **FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BL86**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364603  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BL86  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,  
BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 1500LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1346.9 lumens  
Efficiency: N/A  
Efficacy: 94.9 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364603

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BL86

### Luminous Intensity Polar Plot





TEST NUMBER: P364603

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BL86

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	51825
5°	50839
10°	46950
15°	41836
20°	35728
25°	30006
30°	23555
35°	12208
40°	5830
45°	2295
50°	603
55°	171
60°	109
65°	97
70°	80
75°	106
80°	79
85°	157



TEST NUMBER: P364603

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BL86

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.9	12.8
10°-20°	411.2	30.5
20°-30°	454.0	33.7
30°-40°	249.8	18.5
40°-50°	52.8	3.9
50°-60°	4.5	0.3
60°-70°	1.4	0.1
70°-80°	1.0	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1037.1	77.0
0°-40°	1286.9	95.5
0°-60°	1344.1	99.8
0°-90°	1346.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1346.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1897	
5°	1854	172
15°	1479	411
25°	996	454
35°	366	250
45°	59	53
55°	4	4
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P364603

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BL86

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1897.3
2.5°	1896.3
5°	1854.1
7.5°	1789.1
10°	1692.7
12.5°	1596.7
15°	1479.4
17.5°	1360.1
20°	1229.1
22.5°	1114.4
25°	995.6
27.5°	880.9
30°	746.8
32.5°	570.1
35°	366.1
37.5°	246.7
40°	163.5
42.5°	102.0
45°	59.4
47.5°	30.5
50°	14.2
52.5°	6.1
55°	3.6
57.5°	2.5
60°	2.0
62.5°	1.5
65°	1.5
67.5°	1.0
70°	1.0
72.5°	1.5
75°	1.0
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)