

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365372

Luminaire Tested: **FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BTR89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-12)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BTR89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM ACRYLIC, CLEAR 0.125", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1260.0 lumens
Efficiency: N/A
Efficacy: 62.1 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365372

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BTR89BV

Luminous Intensity Polar Plot





TEST NUMBER: P365372

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BTR89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	82	76	72	80	75	71		78	74	70		76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	72	65	60	81	71	64	60	69	64	59		68	63	59		66	62	58	57
7	78	67	60	55	76	66	60	55	65	59	55		64	58	54		62	58	54	53
8	73	63	56	51	72	62	56	51	61	55	51		60	54	51		59	54	50	49
9	70	59	52	48	68	58	52	48	57	51	47		56	51	47		55	51	47	46
10	66	55	49	45	65	55	49	45	54	48	44		53	48	44		52	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88027
5°	86286
10°	82151
15°	76730
20°	69911
25°	58360
30°	41959
35°	28968
40°	21171
45°	17153
50°	14971
55°	13257
60°	11557
65°	9793
70°	7872
75°	5588
80°	3876
85°	4436



TEST NUMBER: P365372

CATALOG NUMBER: FLD6BX20D010-FEUG6B12-8030-F6LBXVM1-MW-BTR89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.5	8.9
10°-20°	289.5	23.0
20°-30°	330.9	26.3
30°-40°	212.9	16.9
40°-50°	133.4	10.6
50°-60°	95.3	7.6
60°-70°	57.8	4.6
70°-80°	22.6	1.8
80°-90°	5.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	732.9	58.2
0°-40°	945.8	75.1
0°-60°	1174.5	93.2
0°-90°	1260.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1260.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1229	
5°	1200	112
15°	1035	289
25°	739	331
35°	331	213
45°	169	133
55°	106	95
65°	58	58
75°	20	23
85°	5	5
90°	0	



TEST NUMBER: P365372

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BTR89BV

CANDELA DISTRIBUTION (FULL):

0°	
0°	1229.4
2.5°	1223.4
5°	1200.5
7.5°	1172.9
10°	1129.9
12.5°	1086.2
15°	1035.1
17.5°	982.7
20°	917.5
22.5°	836.9
25°	738.7
27.5°	620.4
30°	507.5
32.5°	408.0
35°	331.4
37.5°	270.9
40°	226.5
42.5°	193.6
45°	169.4
47.5°	150.6
50°	134.4
52.5°	120.3
55°	106.2
57.5°	92.8
60°	80.7
62.5°	69.2
65°	57.8
67.5°	47.7
70°	37.6
72.5°	28.2
75°	20.2
77.5°	14.1
80°	9.4
82.5°	6.0
85°	5.4
87.5°	2.7
90°	0.0

(END OF REPORT)