

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364615

Luminaire Tested: **FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BTR89BI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364615  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BTR89BI  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 1500LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1132.0 lumens  
Efficiency: N/A  
Efficacy: 79.7 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364615

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BTR89BI

### Luminous Intensity Polar Plot





TEST NUMBER: P364615

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BTR89BI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	79
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	126843
5°	123899
10°	113873
15°	101347
20°	85844
25°	68259
30°	47995
35°	20026
40°	6917
45°	1792
50°	902
55°	836
60°	816
65°	813
70°	796
75°	1051
80°	1196
85°	1972



TEST NUMBER: P364615

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BTR89BI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.6	14.1
10°-20°	378.7	33.5
20°-30°	390.8	34.5
30°-40°	166.2	14.7
40°-50°	19.9	1.8
50°-60°	6.0	0.5
60°-70°	4.7	0.4
70°-80°	3.8	0.3
80°-90°	2.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	929.1	82.1
0°-40°	1095.3	96.8
0°-60°	1121.3	99.1
0°-90°	1132.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1132.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1772	
5°	1724	160
15°	1367	379
25°	864	391
35°	229	166
45°	18	20
55°	7	6
65°	5	5
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P364615

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-LI-BTR89BI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1771.5
2.5°	1760.0
5°	1723.8
7.5°	1660.7
10°	1566.2
12.5°	1473.1
15°	1367.2
17.5°	1247.8
20°	1126.6
22.5°	1000.1
25°	864.0
27.5°	723.7
30°	580.5
32.5°	411.5
35°	229.1
37.5°	131.8
40°	74.0
42.5°	38.2
45°	17.7
47.5°	9.5
50°	8.1
52.5°	7.2
55°	6.7
57.5°	6.2
60°	5.7
62.5°	5.3
65°	4.8
67.5°	4.3
70°	3.8
72.5°	3.8
75°	3.8
77.5°	3.3
80°	2.9
82.5°	2.9
85°	2.4
87.5°	1.4
90°	0.0

(END OF REPORT)