

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366077

Luminaire Tested: **FLD6BX20D010-FEU6B12-8030-F6LBXVM1-WMH-BL84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-WMH-BL84
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1763.0 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366077

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-WMH-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P366077

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-WMH-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62022
5°	61760
10°	58669
15°	53291
20°	46373
25°	39425
30°	31014
35°	17697
40°	7962
45°	3353
50°	1058
55°	319
60°	219
65°	175
70°	160
75°	211
80°	110
85°	219



TEST NUMBER: P366077

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-WMH-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.7	12.0
10°-20°	524.2	29.7
20°-30°	594.0	33.7
30°-40°	344.4	19.5
40°-50°	76.4	4.3
50°-60°	8.4	0.5
60°-70°	2.7	0.2
70°-80°	1.8	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	1328.9	75.4
0°-40°	1673.3	94.9
0°-60°	1758.0	99.7
0°-90°	1763.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1763.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2271	
5°	2252	211
15°	1884	524
25°	1308	594
35°	531	344
45°	87	76
55°	7	8
65°	3	3
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P366077

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-WMH-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	2270.6
2.5°	2272.6
5°	2252.4
7.5°	2203.3
10°	2115.2
12.5°	2008.3
15°	1884.5
17.5°	1754.0
20°	1595.3
22.5°	1452.1
25°	1308.1
27.5°	1154.8
30°	983.3
32.5°	780.8
35°	530.7
37.5°	341.0
40°	223.3
42.5°	145.9
45°	86.8
47.5°	48.4
50°	24.9
52.5°	11.4
55°	6.7
57.5°	5.4
60°	4.0
62.5°	3.4
65°	2.7
67.5°	2.0
70°	2.0
72.5°	2.0
75°	2.0
77.5°	1.3
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)