

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365323

Luminaire Tested: **FLD6BX15D010-FEU6B12-8050-F6LBXVM1-MW-BL86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365323
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-38)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-MW-BL86
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1169.0 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365323

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-MW-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P365323

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-MW-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	64	57	52	62	56	52		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25944
5°	25336
10°	24025
15°	22499
20°	21011
25°	19343
30°	16534
35°	12575
40°	9217
45°	7015
50°	5724
55°	5038
60°	4480
65°	3936
70°	3338
75°	2617
80°	1793
85°	815



TEST NUMBER: P365323

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-MW-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.4	7.4
10°-20°	223.6	19.1
20°-30°	291.2	24.9
30°-40°	237.6	20.3
40°-50°	143.6	12.3
50°-60°	95.2	8.1
60°-70°	60.6	5.2
70°-80°	26.8	2.3
80°-90°	4.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	601.1	51.4
0°-40°	838.8	71.7
0°-60°	1077.6	92.2
0°-90°	1169.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1169.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	950	
5°	924	86
15°	796	224
25°	642	291
35°	377	238
45°	182	144
55°	106	95
65°	61	61
75°	25	27
85°	3	4
90°	0	



TEST NUMBER: P365323

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-MW-BL86

CANDELA DISTRIBUTION (FULL):

0°	
0°	949.8
2.5°	940.0
5°	924.0
7.5°	898.7
10°	866.2
12.5°	833.2
15°	795.6
17.5°	761.5
20°	722.8
22.5°	685.7
25°	641.8
27.5°	588.2
30°	524.2
32.5°	452.5
35°	377.1
37.5°	313.2
40°	258.5
42.5°	215.1
45°	181.6
47.5°	155.3
50°	134.7
52.5°	118.7
55°	105.8
57.5°	93.4
60°	82.0
62.5°	71.2
65°	60.9
67.5°	51.1
70°	41.8
72.5°	33.0
75°	24.8
77.5°	17.5
80°	11.4
82.5°	6.2
85°	2.6
87.5°	0.5
90°	0.0

(END OF REPORT)