

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364660

Luminaire Tested: **FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BL89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-41)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BL89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS ACRYLIC, CLEAR 0.125", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1913.0 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364660

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P364660

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 |
| 2 | 109 | 104 | 100 | 97 | 106 | 102 | 99 | 96 | 99 | 96 | 94 | 96 | 94 | 92 | 93 | 91 | 90 | 88 |
| 3 | 103 | 97 | 93 | 89 | 101 | 96 | 92 | 88 | 93 | 90 | 87 | 91 | 88 | 85 | 89 | 86 | 84 | 83 |
| 4 | 99 | 91 | 86 | 82 | 97 | 90 | 85 | 82 | 88 | 84 | 81 | 86 | 83 | 80 | 84 | 81 | 79 | 77 |
| 5 | 94 | 86 | 81 | 76 | 92 | 85 | 80 | 76 | 83 | 79 | 75 | 82 | 78 | 75 | 80 | 77 | 74 | 73 |
| 6 | 90 | 81 | 75 | 71 | 88 | 80 | 75 | 71 | 79 | 74 | 71 | 77 | 73 | 70 | 76 | 73 | 70 | 68 |
| 7 | 85 | 77 | 71 | 67 | 84 | 76 | 71 | 67 | 75 | 70 | 66 | 74 | 69 | 66 | 72 | 69 | 66 | 64 |
| 8 | 82 | 73 | 67 | 63 | 80 | 72 | 67 | 63 | 71 | 66 | 63 | 70 | 65 | 62 | 69 | 65 | 62 | 61 |
| 9 | 78 | 69 | 63 | 59 | 77 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 59 | 66 | 62 | 59 | 57 |
| 10 | 74 | 65 | 60 | 56 | 74 | 65 | 60 | 56 | 64 | 59 | 56 | 63 | 59 | 56 | 63 | 59 | 56 | 54 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 74065 |
| 5° | 72561 |
| 10° | 66987 |
| 15° | 59547 |
| 20° | 50817 |
| 25° | 42577 |
| 30° | 33370 |
| 35° | 17593 |
| 40° | 8219 |
| 45° | 3233 |
| 50° | 846 |
| 55° | 229 |
| 60° | 148 |
| 65° | 136 |
| 70° | 112 |
| 75° | 148 |
| 80° | 110 |
| 85° | 219 |



TEST NUMBER: P364660

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BL89BV

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 244.9 | 12.8 |
| 10°-20° | 584.8 | 30.6 |
| 20°-30° | 643.2 | 33.6 |
| 30°-40° | 355.1 | 18.6 |
| 40°-50° | 74.9 | 3.9 |
| 50°-60° | 6.1 | 0.3 |
| 60°-70° | 1.9 | 0.1 |
| 70°-80° | 1.6 | 0.1 |
| 80°-90° | 0.7 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1472.9 | 77.0 |
| 0°-40° | 1827.9 | 95.5 |
| 0°-60° | 1908.9 | 99.8 |
| 0°-90° | 1913.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1913.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2712 | |
| 5° | 2646 | 245 |
| 15° | 2106 | 585 |
| 25° | 1413 | 643 |
| 35° | 528 | 355 |
| 45° | 84 | 75 |
| 55° | 5 | 6 |
| 65° | 2 | 2 |
| 75° | 1 | 2 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P364660

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2711.5 |
| 2.5° | 2690.9 |
| 5° | 2646.3 |
| 7.5° | 2545.4 |
| 10° | 2415.1 |
| 12.5° | 2265.5 |
| 15° | 2105.7 |
| 17.5° | 1934.1 |
| 20° | 1748.2 |
| 22.5° | 1579.4 |
| 25° | 1412.7 |
| 27.5° | 1243.2 |
| 30° | 1058.0 |
| 32.5° | 805.5 |
| 35° | 527.6 |
| 37.5° | 350.6 |
| 40° | 230.5 |
| 42.5° | 145.5 |
| 45° | 83.7 |
| 47.5° | 43.9 |
| 50° | 19.9 |
| 52.5° | 8.2 |
| 55° | 4.8 |
| 57.5° | 3.4 |
| 60° | 2.7 |
| 62.5° | 2.1 |
| 65° | 2.1 |
| 67.5° | 1.4 |
| 70° | 1.4 |
| 72.5° | 2.1 |
| 75° | 1.4 |
| 77.5° | 1.4 |
| 80° | 0.7 |
| 82.5° | 0.7 |
| 85° | 0.7 |
| 87.5° | 0.7 |
| 90° | 0.0 |

(END OF REPORT)