

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365333

Luminaire Tested: **FLD6BX15D010-FEU6B12-8050-F6LBXVM1-MW-BTR86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365333
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-17)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-MW-BTR86
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 1500LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 882.0 lumens
Efficiency: N/A
Efficacy: 62.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 14.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365333

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-MW-BTR86

Luminous Intensity Polar Plot





TEST NUMBER: P365333

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-MW-BTR86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	98	93	89	94	91	87		91	88	85		88	86	84	82
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82	79	76	74
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	72	69	68
5	87	78	71	66	86	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	66	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	51	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		53	48	45		53	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62387
5°	61252
10°	58172
15°	54373
20°	49200
25°	40861
30°	29318
35°	20122
40°	14815
45°	11969
50°	10404
55°	9150
60°	7905
65°	6726
70°	5297
75°	3707
80°	2350
85°	2547



TEST NUMBER: P365333

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-MW-BTR86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.7	9.0
10°-20°	204.7	23.2
20°-30°	232.1	26.3
30°-40°	148.8	16.9
40°-50°	93.3	10.6
50°-60°	65.8	7.5
60°-70°	39.5	4.5
70°-80°	15.1	1.7
80°-90°	3.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	516.5	58.6
0°-40°	665.3	75.4
0°-60°	824.4	93.5
0°-90°	882.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	882.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	871	
5°	852	80
15°	734	205
25°	517	232
35°	230	149
45°	118	93
55°	73	66
65°	40	40
75°	13	15
85°	3	3
90°	0	



TEST NUMBER: P365333

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-MW-BTR86

CANDELA DISTRIBUTION (FULL):

	0°
0°	871.3
2.5°	868.7
5°	852.2
7.5°	830.0
10°	800.1
12.5°	767.6
15°	733.5
17.5°	694.8
20°	645.7
22.5°	588.4
25°	517.2
27.5°	435.1
30°	354.6
32.5°	286.5
35°	230.2
37.5°	189.4
40°	158.5
42.5°	135.8
45°	118.2
47.5°	105.3
50°	93.4
52.5°	83.1
55°	73.3
57.5°	64.0
60°	55.2
62.5°	47.5
65°	39.7
67.5°	32.5
70°	25.3
72.5°	19.1
75°	13.4
77.5°	9.3
80°	5.7
82.5°	3.6
85°	3.1
87.5°	1.5
90°	0.0

(END OF REPORT)