

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366098

Luminaire Tested: **FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BL87**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366098  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BL87  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 2000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1697.9 lumens  
Efficiency: N/A  
Efficacy: 83.6 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366098

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BL87

### Luminous Intensity Polar Plot





TEST NUMBER: P366098

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BL87

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	84	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	59736
5°	59484
10°	56505
15°	51326
20°	44663
25°	37972
30°	29869
35°	17043
40°	7670
45°	3229
50°	1020
55°	310
60°	213
65°	168
70°	152
75°	201
80°	94
85°	188



TEST NUMBER: P366098

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BL87

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.9	12.0
10°-20°	504.9	29.7
20°-30°	572.1	33.7
30°-40°	331.7	19.5
40°-50°	73.6	4.3
50°-60°	8.1	0.5
60°-70°	2.6	0.2
70°-80°	1.7	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	1279.9	75.4
0°-40°	1611.6	94.9
0°-60°	1693.2	99.7
0°-90°	1697.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1697.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2187	
5°	2169	203
15°	1815	505
25°	1260	572
35°	511	332
45°	84	74
55°	6	8
65°	3	3
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P366098

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BL87

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2186.9
2.5°	2188.8
5°	2169.4
7.5°	2122.1
10°	2037.2
12.5°	1934.2
15°	1815.0
17.5°	1689.4
20°	1536.5
22.5°	1398.5
25°	1259.9
27.5°	1112.2
30°	947.0
32.5°	752.1
35°	511.1
37.5°	328.4
40°	215.1
42.5°	140.6
45°	83.6
47.5°	46.6
50°	24.0
52.5°	11.0
55°	6.5
57.5°	5.2
60°	3.9
62.5°	3.2
65°	2.6
67.5°	1.9
70°	1.9
72.5°	1.9
75°	1.9
77.5°	1.3
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)