

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366106

Luminaire Tested: **FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR85**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366106  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR85  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,  
BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 2000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1517.0 lumens  
Efficiency: N/A  
Efficacy: 74.7 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366106

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR85

### Luminous Intensity Polar Plot





TEST NUMBER: P366106

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR85

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	156844
5°	154259
10°	146983
15°	134312
20°	115180
25°	92419
30°	64795
35°	29938
40°	9609
45°	3099
50°	1437
55°	1273
60°	1275
65°	1152
70°	1130
75°	1328
80°	1691
85°	2793



TEST NUMBER: P366106

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR85

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	201.3	13.3
10°-20°	501.4	33.1
20°-30°	526.6	34.7
30°-40°	233.7	15.4
40°-50°	30.2	2.0
50°-60°	9.4	0.6
60°-70°	6.6	0.4
70°-80°	4.9	0.3
80°-90°	3.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1229.2	81.0
0°-40°	1462.9	96.4
0°-60°	1502.5	99.0
0°-90°	1517.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1517.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2190	
5°	2146	201
15°	1812	501
25°	1170	527
35°	342	234
45°	31	30
55°	10	9
65°	7	7
75°	5	5
85°	3	3
90°	0	



TEST NUMBER: P366106

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR85

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2190.5
2.5°	2176.9
5°	2146.2
7.5°	2104.7
10°	2021.6
12.5°	1928.3
15°	1811.9
17.5°	1672.3
20°	1511.6
22.5°	1342.7
25°	1169.8
27.5°	975.7
30°	783.7
32.5°	576.0
35°	342.5
37.5°	182.5
40°	102.8
42.5°	56.5
45°	30.6
47.5°	15.7
50°	12.9
52.5°	11.6
55°	10.2
57.5°	9.5
60°	8.9
62.5°	7.5
65°	6.8
67.5°	5.4
70°	5.4
72.5°	4.8
75°	4.8
77.5°	4.1
80°	4.1
82.5°	3.4
85°	3.4
87.5°	2.0
90°	0.0

(END OF REPORT)