

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366111

Luminaire Tested: **FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR94**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366111
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-33)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR94
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM GLASS, TEMPERED CLEAR 0.187", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1553.1 lumens
Efficiency: N/A
Efficacy: 76.5 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366111

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR94

Luminous Intensity Polar Plot





TEST NUMBER: P366111

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR94

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	73	71	69
7	86	78	72	68	85	77	72	68	76	71	67		74	70	67		73	70	67	65
8	82	74	68	64	81	73	68	64	72	67	64		71	67	63		70	66	63	62
9	79	70	64	61	78	69	64	61	68	64	60		68	63	60		67	63	60	59
10	76	66	61	57	75	66	61	57	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159708
5°	157903
10°	149906
15°	136514
20°	117488
25°	94125
30°	66408
35°	30759
40°	10001
45°	3200
50°	1526
55°	1373
60°	1275
65°	1169
70°	1151
75°	1522
80°	1691
85°	2793



TEST NUMBER: P366111

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR94

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.3	13.2
10°-20°	510.7	32.9
20°-30°	539.0	34.7
30°-40°	241.2	15.5
40°-50°	31.6	2.0
50°-60°	9.7	0.6
60°-70°	6.9	0.4
70°-80°	5.4	0.4
80°-90°	3.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1255.0	80.8
0°-40°	1496.2	96.3
0°-60°	1537.6	99.0
0°-90°	1553.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1553.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2230	
5°	2197	205
15°	1842	511
25°	1191	539
35°	352	241
45°	32	32
55°	11	10
65°	7	7
75°	6	5
85°	3	3
90°	0	



TEST NUMBER: P366111

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-WMH-BTR94

CANDELA DISTRIBUTION (FULL):

	0°
0°	2230.5
2.5°	2216.1
5°	2196.9
7.5°	2142.7
10°	2061.8
12.5°	1965.1
15°	1841.6
17.5°	1704.4
20°	1541.9
22.5°	1376.6
25°	1191.4
27.5°	1004.1
30°	803.2
32.5°	595.4
35°	351.9
37.5°	191.4
40°	107.0
42.5°	59.7
45°	31.6
47.5°	16.5
50°	13.7
52.5°	11.7
55°	11.0
57.5°	9.6
60°	8.9
62.5°	7.5
65°	6.9
67.5°	6.2
70°	5.5
72.5°	5.5
75°	5.5
77.5°	4.8
80°	4.1
82.5°	4.1
85°	3.4
87.5°	2.1
90°	0.0

(END OF REPORT)