

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366055

Luminaire Tested: **FLD6BX15D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366055  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BI  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,  
BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 1500LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1110.0 lumens  
Efficiency: N/A  
Efficacy: 78.2 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366055

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BI

### Luminous Intensity Polar Plot





TEST NUMBER: P366055

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	114978
5°	113427
10°	107969
15°	98152
20°	84518
25°	67564
30°	47375
35°	22036
40°	6963
45°	2177
50°	958
55°	899
60°	816
65°	729
70°	796
75°	913
80°	1196
85°	1972



TEST NUMBER: P366055

CATALOG NUMBER: FLD6BX15D010-FEUG6B12-8050-F6LBXVM1-WMH-BTR89BI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.7	13.3
10°-20°	367.1	33.1
20°-30°	386.0	34.8
30°-40°	171.2	15.4
40°-50°	21.4	1.9
50°-60°	6.4	0.6
60°-70°	4.5	0.4
70°-80°	3.5	0.3
80°-90°	2.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	900.8	81.2
0°-40°	1072.1	96.6
0°-60°	1099.9	99.1
0°-90°	1110.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1110.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1606	
5°	1578	148
15°	1324	367
25°	855	386
35°	252	171
45°	22	21
55°	7	6
65°	4	4
75°	3	4
85°	2	2
90°	0	



TEST NUMBER: P366055

CATALOG NUMBER: FLD6BX15D010-FEU6B12-8050-F6LBXVM1-WMH-BTR89BI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1605.8
2.5°	1595.3
5°	1578.1
7.5°	1542.8
10°	1485.0
12.5°	1414.3
15°	1324.1
17.5°	1222.4
20°	1109.2
22.5°	986.5
25°	855.2
27.5°	715.8
30°	573.0
32.5°	421.6
35°	252.1
37.5°	134.2
40°	74.5
42.5°	40.6
45°	21.5
47.5°	10.5
50°	8.6
52.5°	7.6
55°	7.2
57.5°	6.7
60°	5.7
62.5°	5.3
65°	4.3
67.5°	3.8
70°	3.8
72.5°	3.3
75°	3.3
77.5°	3.3
80°	2.9
82.5°	2.4
85°	2.4
87.5°	1.4
90°	0.0

(END OF REPORT)