

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364673

Luminaire Tested: **FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364673
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL84
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1840.0 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364673

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P364673

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 |
| 2 | 109 | 104 | 100 | 97 | 106 | 102 | 99 | 96 | 99 | 96 | 94 | 96 | 94 | 92 | 93 | 91 | 90 | 88 |
| 3 | 103 | 97 | 93 | 89 | 101 | 96 | 92 | 88 | 93 | 90 | 87 | 91 | 88 | 85 | 89 | 86 | 84 | 83 |
| 4 | 99 | 91 | 86 | 82 | 97 | 90 | 85 | 82 | 88 | 84 | 81 | 86 | 83 | 80 | 84 | 81 | 79 | 77 |
| 5 | 94 | 86 | 80 | 76 | 92 | 85 | 80 | 76 | 83 | 79 | 75 | 82 | 78 | 75 | 80 | 77 | 74 | 73 |
| 6 | 90 | 81 | 75 | 71 | 88 | 80 | 75 | 71 | 79 | 74 | 71 | 77 | 73 | 70 | 76 | 73 | 70 | 68 |
| 7 | 85 | 77 | 71 | 67 | 84 | 76 | 71 | 67 | 75 | 70 | 66 | 74 | 69 | 66 | 72 | 69 | 66 | 64 |
| 8 | 82 | 72 | 67 | 63 | 80 | 72 | 67 | 63 | 71 | 66 | 63 | 70 | 65 | 62 | 69 | 65 | 62 | 61 |
| 9 | 78 | 69 | 63 | 59 | 77 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 59 | 66 | 62 | 59 | 57 |
| 10 | 74 | 65 | 60 | 56 | 73 | 65 | 60 | 56 | 64 | 59 | 56 | 63 | 59 | 56 | 63 | 58 | 56 | 54 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 70793 |
| 5° | 69446 |
| 10° | 64133 |
| 15° | 57149 |
| 20° | 48806 |
| 25° | 40989 |
| 30° | 32178 |
| 35° | 16673 |
| 40° | 7962 |
| 45° | 3133 |
| 50° | 824 |
| 55° | 233 |
| 60° | 153 |
| 65° | 136 |
| 70° | 112 |
| 75° | 148 |
| 80° | 110 |
| 85° | 219 |



TEST NUMBER: P364673

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL84

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 234.9 | 12.8 |
| 10°-20° | 561.7 | 30.5 |
| 20°-30° | 620.1 | 33.7 |
| 30°-40° | 341.2 | 18.5 |
| 40°-50° | 72.1 | 3.9 |
| 50°-60° | 6.1 | 0.3 |
| 60°-70° | 1.9 | 0.1 |
| 70°-80° | 1.4 | 0.1 |
| 80°-90° | 0.7 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1416.6 | 77.0 |
| 0°-40° | 1757.9 | 95.5 |
| 0°-60° | 1836.1 | 99.8 |
| 0°-90° | 1840.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1840.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2592 | |
| 5° | 2533 | 235 |
| 15° | 2021 | 562 |
| 25° | 1360 | 620 |
| 35° | 500 | 341 |
| 45° | 81 | 72 |
| 55° | 5 | 6 |
| 65° | 2 | 2 |
| 75° | 1 | 1 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P364673

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-LI-BL84

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2591.7 |
| 2.5° | 2590.3 |
| 5° | 2532.7 |
| 7.5° | 2444.0 |
| 10° | 2312.2 |
| 12.5° | 2181.1 |
| 15° | 2020.9 |
| 17.5° | 1857.9 |
| 20° | 1679.0 |
| 22.5° | 1522.3 |
| 25° | 1360.0 |
| 27.5° | 1203.3 |
| 30° | 1020.2 |
| 32.5° | 778.8 |
| 35° | 500.0 |
| 37.5° | 337.0 |
| 40° | 223.3 |
| 42.5° | 139.4 |
| 45° | 81.1 |
| 47.5° | 41.6 |
| 50° | 19.4 |
| 52.5° | 8.3 |
| 55° | 4.9 |
| 57.5° | 3.5 |
| 60° | 2.8 |
| 62.5° | 2.1 |
| 65° | 2.1 |
| 67.5° | 1.4 |
| 70° | 1.4 |
| 72.5° | 2.1 |
| 75° | 1.4 |
| 77.5° | 0.7 |
| 80° | 0.7 |
| 82.5° | 0.7 |
| 85° | 0.7 |
| 87.5° | 0.7 |
| 90° | 0.0 |

(END OF REPORT)