

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366060

Luminaire Tested: **FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BL85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366060
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BL85
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1680.9 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366060

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P366060

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	84	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59138
5°	58886
10°	55939
15°	50814
20°	44216
25°	37592
30°	29570
35°	16873
40°	7591
45°	3195
50°	1007
55°	305
60°	208
65°	168
70°	152
75°	201
80°	94
85°	188



TEST NUMBER: P366060

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.9	12.0
10°-20°	499.8	29.7
20°-30°	566.4	33.7
30°-40°	328.3	19.5
40°-50°	72.8	4.3
50°-60°	8.0	0.5
60°-70°	2.6	0.2
70°-80°	1.7	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1267.1	75.4
0°-40°	1595.5	94.9
0°-60°	1676.2	99.7
0°-90°	1680.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1680.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2165	
5°	2148	201
15°	1797	500
25°	1247	566
35°	506	328
45°	83	73
55°	6	8
65°	3	3
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P366060

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8027-F6LBXVM1-WMH-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	2165.0
2.5°	2166.9
5°	2147.6
7.5°	2100.8
10°	2016.8
12.5°	1914.9
15°	1796.9
17.5°	1672.5
20°	1521.1
22.5°	1384.5
25°	1247.3
27.5°	1101.1
30°	937.5
32.5°	744.5
35°	506.0
37.5°	325.1
40°	212.9
42.5°	139.2
45°	82.7
47.5°	46.2
50°	23.7
52.5°	10.9
55°	6.4
57.5°	5.1
60°	3.8
62.5°	3.2
65°	2.6
67.5°	1.9
70°	1.9
72.5°	1.9
75°	1.9
77.5°	1.3
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)