

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366129

Luminaire Tested: **FLD6BX20D010-FEU6B12-8040-F6LBXVM1-WMH-BTR94**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366129
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-33)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-WMH-BTR94
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM GLASS, TEMPERED CLEAR 0.187", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1570.0 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366129

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-WMH-BTR94

Luminous Intensity Polar Plot





TEST NUMBER: P366129

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-WMH-BTR94

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76	82	78	75	81	77	75	73
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	73	71	69
7	86	78	72	68	85	77	72	68	76	71	67	74	70	67	73	70	67	65
8	82	74	68	64	81	73	68	64	72	67	64	71	67	63	70	66	63	62
9	79	70	64	61	78	69	64	61	68	64	60	68	63	60	67	63	60	59
10	76	66	61	57	75	66	61	57	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	161455
5°	159628
10°	151542
15°	138011
20°	118776
25°	95152
30°	67135
35°	31092
40°	10113
45°	3230
50°	1548
55°	1386
60°	1289
65°	1169
70°	1151
75°	1522
80°	1732
85°	2875



TEST NUMBER: P366129

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-WMH-BTR94

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.5	13.2
10°-20°	516.3	32.9
20°-30°	544.9	34.7
30°-40°	243.9	15.5
40°-50°	31.9	2.0
50°-60°	9.8	0.6
60°-70°	6.9	0.4
70°-80°	5.5	0.3
80°-90°	3.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1268.7	80.8
0°-40°	1512.6	96.3
0°-60°	1554.4	99.0
0°-90°	1570.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1570.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2255	
5°	2221	208
15°	1862	516
25°	1204	545
35°	356	244
45°	32	32
55°	11	10
65°	7	7
75°	6	5
85°	4	3
90°	0	



TEST NUMBER: P366129

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8040-F6LBXVM1-WMH-BTR94

CANDELA DISTRIBUTION (FULL):

	0°
0°	2254.9
2.5°	2240.4
5°	2220.9
7.5°	2166.2
10°	2084.3
12.5°	1986.6
15°	1861.8
17.5°	1723.1
20°	1558.8
22.5°	1391.6
25°	1204.4
27.5°	1015.1
30°	812.0
32.5°	601.9
35°	355.7
37.5°	193.5
40°	108.2
42.5°	60.3
45°	31.9
47.5°	16.6
50°	13.9
52.5°	11.8
55°	11.1
57.5°	9.7
60°	9.0
62.5°	7.6
65°	6.9
67.5°	6.2
70°	5.5
72.5°	5.5
75°	5.5
77.5°	4.9
80°	4.2
82.5°	4.2
85°	3.5
87.5°	2.1
90°	0.0

(END OF REPORT)