

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364637

Luminaire Tested: **FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BL84**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364637  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BL84  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,  
BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 2000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1784.0 lumens  
Efficiency: N/A  
Efficacy: 87.9 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364637

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BL84

### Luminous Intensity Polar Plot





TEST NUMBER: P364637

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BL84

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	68638
5°	67332
10°	62180
15°	55410
20°	47320
25°	39741
30°	31197
35°	16166
40°	7720
45°	3040
50°	799
55°	224
60°	148
65°	129
70°	104
75°	137
80°	110
85°	219



TEST NUMBER: P364637

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BL84

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	227.7	12.8
10°-20°	544.6	30.5
20°-30°	601.2	33.7
30°-40°	330.8	18.5
40°-50°	69.9	3.9
50°-60°	5.9	0.3
60°-70°	1.8	0.1
70°-80°	1.3	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1373.5	77.0
0°-40°	1704.3	95.5
0°-60°	1780.2	99.8
0°-90°	1784.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1784.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2513	
5°	2456	228
15°	1959	545
25°	1319	601
35°	485	331
45°	79	70
55°	5	6
65°	2	2
75°	1	1
85°	1	1
90°	0	



TEST NUMBER: P364637

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BL84

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2512.8
2.5°	2511.5
5°	2455.6
7.5°	2369.6
10°	2241.8
12.5°	2114.7
15°	1959.4
17.5°	1801.4
20°	1627.9
22.5°	1475.9
25°	1318.6
27.5°	1166.6
30°	989.1
32.5°	755.1
35°	484.8
37.5°	326.8
40°	216.5
42.5°	135.2
45°	78.7
47.5°	40.3
50°	18.8
52.5°	8.1
55°	4.7
57.5°	3.4
60°	2.7
62.5°	2.0
65°	2.0
67.5°	1.3
70°	1.3
72.5°	2.0
75°	1.3
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)