

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364641

Luminaire Tested: **FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BL89AM**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-44)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BL89AM
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, OPAL SMOOTH 0.125", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 772.0 lumens
Efficiency: N/A
Efficacy: 38.0 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364641

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P364641

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	94	98	94	91		94	91	89		90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	75		82	78	74		79	75	72	70
3	90	80	71	65	88	78	70	64	75	68	63		72	67	62		70	65	61	59
4	82	70	62	55	80	69	61	54	67	59	54		64	58	53		62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	46		58	51	46		56	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41		52	45	40		51	45	40	38
7	65	51	42	36	63	50	42	36	49	41	36		47	41	36		46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32		43	37	32		42	36	32	30
9	56	43	35	29	55	42	34	29	41	34	29		40	33	29		39	33	29	27
10	53	40	32	26	52	39	31	26	38	31	26		37	31	26		36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7457
5°	7428
10°	7403
15°	7378
20°	7328
25°	7276
30°	7232
35°	7153
40°	7096
45°	7011
50°	6914
55°	6758
60°	6572
65°	6302
70°	5854
75°	5182
80°	4231
85°	2727



TEST NUMBER: P364641

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.8	3.3
10°-20°	73.6	9.5
20°-30°	111.4	14.4
30°-40°	134.3	17.4
40°-50°	139.9	18.1
50°-60°	127.0	16.4
60°-70°	96.1	12.5
70°-80°	52.4	6.8
80°-90°	11.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	210.8	27.3
0°-40°	345.1	44.7
0°-60°	612.0	79.3
0°-90°	772.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	772.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	273	
5°	271	26
15°	261	74
25°	241	111
35°	214	134
45°	182	140
55°	142	127
65°	98	96
75°	49	52
85°	9	12
90°	0	



TEST NUMBER: P364641

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	273.0
2.5°	272.3
5°	270.9
7.5°	269.6
10°	266.9
12.5°	264.2
15°	260.9
17.5°	256.8
20°	252.1
22.5°	247.4
25°	241.4
27.5°	236.0
30°	229.3
32.5°	222.5
35°	214.5
37.5°	206.4
40°	199.0
42.5°	190.3
45°	181.5
47.5°	172.1
50°	162.7
52.5°	152.6
55°	141.9
57.5°	131.8
60°	120.3
62.5°	108.9
65°	97.5
67.5°	85.4
70°	73.3
72.5°	61.9
75°	49.1
77.5°	37.7
80°	26.9
82.5°	16.8
85°	8.7
87.5°	3.4
90°	0.0

(END OF REPORT)