

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365413

Luminaire Tested: **FLD6BX20D010-FEU6B12-8050-F6LBXVM1-MW-BL86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365413
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-38)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-MW-BL86
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1609.0 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365413

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-MW-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P365413

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-MW-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		83	78	75		80	77	74	72
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	64	57	52	62	56	52		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35709
5°	34872
10°	33070
15°	30965
20°	28920
25°	26625
30°	22757
35°	17310
40°	12687
45°	9657
50°	7874
55°	6934
60°	6168
65°	5416
70°	4592
75°	3599
80°	2454
85°	1128



TEST NUMBER: P365413

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-MW-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.9	7.4
10°-20°	307.8	19.1
20°-30°	400.7	24.9
30°-40°	327.1	20.3
40°-50°	197.7	12.3
50°-60°	130.9	8.1
60°-70°	83.4	5.2
70°-80°	36.9	2.3
80°-90°	5.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	827.4	51.4
0°-40°	1154.5	71.8
0°-60°	1483.1	92.2
0°-90°	1609.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1609.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1307	
5°	1272	119
15°	1095	308
25°	883	401
35°	519	327
45°	250	198
55°	146	131
65°	84	83
75°	34	37
85°	4	6
90°	0	



TEST NUMBER: P365413

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-MW-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	1307.3
2.5°	1293.8
5°	1271.8
7.5°	1237.0
10°	1192.3
12.5°	1146.8
15°	1095.0
17.5°	1048.1
20°	994.9
22.5°	943.8
25°	883.4
27.5°	809.5
30°	721.5
32.5°	622.8
35°	519.1
37.5°	431.0
40°	355.8
42.5°	296.1
45°	250.0
47.5°	213.7
50°	185.3
52.5°	163.3
55°	145.6
57.5°	128.5
60°	112.9
62.5°	98.0
65°	83.8
67.5°	70.3
70°	57.5
72.5°	45.4
75°	34.1
77.5°	24.1
80°	15.6
82.5°	8.5
85°	3.6
87.5°	0.7
90°	0.0

(END OF REPORT)