

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364645

Luminaire Tested: **FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR81**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364645
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-25)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR81
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.156", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1483.0 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.19
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364645

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR81

Luminous Intensity Polar Plot





TEST NUMBER: P364645

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR81

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	76	73	72
4	91	81	74	69	89	80	73	68	78	72	68		75	71	67		73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	61		69	64	60		68	63	59	58
6	79	68	61	55	77	67	60	55	66	59	55		64	59	54		63	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50		59	54	49		58	53	49	47
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	42		51	46	41		50	45	41	40
10	62	50	43	39	61	50	43	38	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55119
5°	59146
10°	63742
15°	65581
20°	64950
25°	61236
30°	55527
35°	48425
40°	40594
45°	32677
50°	25164
55°	18301
60°	12416
65°	8200
70°	5338
75°	4094
80°	3587
85°	4436



TEST NUMBER: P364645

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR81

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.3	5.4
10°-20°	248.2	16.7
20°-30°	354.4	23.9
30°-40°	344.8	23.2
40°-50°	249.4	16.8
50°-60°	133.7	9.0
60°-70°	50.4	3.4
70°-80°	16.5	1.1
80°-90°	5.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	682.9	46.1
0°-40°	1027.7	69.3
0°-60°	1410.8	95.1
0°-90°	1483.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1483.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	770	
5°	823	80
15°	885	248
25°	775	354
35°	554	345
45°	323	249
55°	147	134
65°	48	50
75°	15	17
85°	5	5
90°	0	



TEST NUMBER: P364645

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-LI-BTR81

CANDELA DISTRIBUTION (FULL):

0°	
0°	769.8
2.5°	791.9
5°	822.9
7.5°	856.5
10°	876.7
12.5°	885.4
15°	884.7
17.5°	872.6
20°	852.4
22.5°	820.2
25°	775.1
27.5°	726.7
30°	671.6
32.5°	615.1
35°	554.0
37.5°	492.1
40°	434.3
42.5°	375.1
45°	322.7
47.5°	271.6
50°	225.9
52.5°	183.5
55°	146.6
57.5°	115.0
60°	86.7
62.5°	65.2
65°	48.4
67.5°	35.0
70°	25.5
72.5°	19.5
75°	14.8
77.5°	11.4
80°	8.7
82.5°	6.7
85°	5.4
87.5°	2.7
90°	0.0

(END OF REPORT)