

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365426

Luminaire Tested: **FLD6BX20D010-FEU6B12-8050-F6LBXVM1-MW-BTR89BV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365426  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-MW-BTR89BV  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,  
BOTTOM TRIM ACRYLIC, CLEAR 0.125", 2000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1331.0 lumens  
Efficiency: N/A  
Efficacy: 65.6 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365426

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-MW-BTR89BV

### Luminous Intensity Polar Plot





TEST NUMBER: P365426

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-MW-BTR89BV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	82	76	72	80	75	71		78	74	70		76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	72	65	60	81	71	64	60	69	64	59		68	63	59		66	62	58	57
7	78	67	60	55	76	66	60	55	65	59	55		64	58	54		62	58	54	53
8	73	63	56	51	72	62	56	51	61	55	51		60	54	51		59	54	50	49
9	70	59	52	48	68	58	52	48	57	51	47		56	51	47		55	51	47	46
10	66	55	49	45	65	55	49	45	54	48	44		53	48	44		52	48	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	92989
5°	91152
10°	86782
15°	81059
20°	73850
25°	61647
30°	44324
35°	30602
40°	22367
45°	18115
50°	15818
55°	14006
60°	12201
65°	10352
70°	8332
75°	5893
80°	4082
85°	4683



TEST NUMBER: P365426

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-MW-BTR89BV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.8	8.9
10°-20°	305.8	23.0
20°-30°	349.5	26.3
30°-40°	224.9	16.9
40°-50°	140.9	10.6
50°-60°	100.6	7.6
60°-70°	61.0	4.6
70°-80°	23.9	1.8
80°-90°	5.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	774.2	58.2
0°-40°	999.1	75.1
0°-60°	1240.7	93.2
0°-90°	1331.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1331.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1299	
5°	1268	119
15°	1094	306
25°	780	350
35°	350	225
45°	179	141
55°	112	101
65°	61	61
75°	21	24
85°	6	5
90°	0	



TEST NUMBER: P365426

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-MW-BTR89BV

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1298.7
2.5°	1292.3
5°	1268.2
7.5°	1239.0
10°	1193.6
12.5°	1147.4
15°	1093.5
17.5°	1038.1
20°	969.2
22.5°	884.0
25°	780.3
27.5°	655.4
30°	536.1
32.5°	431.0
35°	350.1
37.5°	286.2
40°	239.3
42.5°	204.5
45°	178.9
47.5°	159.1
50°	142.0
52.5°	127.1
55°	112.2
57.5°	98.0
60°	85.2
62.5°	73.1
65°	61.1
67.5°	50.4
70°	39.8
72.5°	29.8
75°	21.3
77.5°	14.9
80°	9.9
82.5°	6.4
85°	5.7
87.5°	2.8
90°	0.0

(END OF REPORT)