

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366141

Luminaire Tested: **FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH-BTR84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366141
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH-BTR84
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1582.1 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366141

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH-BTR84

Luminous Intensity Polar Plot





TEST NUMBER: P366141

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH-BTR84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	163560
5°	160871
10°	153280
15°	140064
20°	120117
25°	96377
30°	67573
35°	31223
40°	10020
45°	3240
50°	1504
55°	1336
60°	1317
65°	1203
70°	1193
75°	1383
80°	1773
85°	2958



TEST NUMBER: P366141

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH-BTR84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.9	13.3
10°-20°	522.9	33.1
20°-30°	549.1	34.7
30°-40°	243.7	15.4
40°-50°	31.5	2.0
50°-60°	9.8	0.6
60°-70°	6.9	0.4
70°-80°	5.1	0.3
80°-90°	3.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1281.9	81.0
0°-40°	1525.6	96.4
0°-60°	1566.9	99.0
0°-90°	1582.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1582.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2284	
5°	2238	210
15°	1890	523
25°	1220	549
35°	357	244
45°	32	31
55°	11	10
65°	7	7
75°	5	5
85°	4	3
90°	0	



TEST NUMBER: P366141

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8050-F6LBXVM1-WMH-BTR84

CANDELA DISTRIBUTION (FULL):

	0°
0°	2284.3
2.5°	2270.1
5°	2238.2
7.5°	2194.9
10°	2108.2
12.5°	2010.9
15°	1889.5
17.5°	1744.0
20°	1576.4
22.5°	1400.3
25°	1219.9
27.5°	1017.5
30°	817.3
32.5°	600.7
35°	357.2
37.5°	190.3
40°	107.2
42.5°	58.9
45°	32.0
47.5°	16.3
50°	13.5
52.5°	12.1
55°	10.7
57.5°	9.9
60°	9.2
62.5°	7.8
65°	7.1
67.5°	5.7
70°	5.7
72.5°	5.0
75°	5.0
77.5°	4.3
80°	4.3
82.5°	3.6
85°	3.6
87.5°	2.1
90°	0.0

(END OF REPORT)