

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365368

Luminaire Tested: **FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BTR85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-16)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BTR85
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1186.0 lumens
Efficiency: N/A
Efficacy: 58.4 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365368

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BTR85

Luminous Intensity Polar Plot





TEST NUMBER: P365368

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BTR85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	82	76	72	80	75	71		78	73	70		76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	72	65	60	80	71	64	60	69	63	59		68	63	59		66	62	58	57
7	77	67	60	55	76	66	60	55	65	59	55		64	58	54		62	58	54	52
8	73	63	56	51	72	62	55	51	61	55	51		60	54	51		59	54	50	49
9	70	59	52	48	68	58	52	48	57	51	47		56	51	47		55	51	47	45
10	66	55	49	45	65	55	49	44	54	48	44		53	48	44		52	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82407
5°	80889
10°	76836
15°	71963
20°	65514
25°	54655
30°	39628
35°	27263
40°	20049
45°	16273
50°	14158
55°	12508
60°	10883
65°	9234
70°	7453
75°	5395
80°	3587
85°	3861



TEST NUMBER: P365368

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BTR85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.2	8.9
10°-20°	271.1	22.9
20°-30°	311.2	26.2
30°-40°	201.4	17.0
40°-50°	126.5	10.7
50°-60°	90.1	7.6
60°-70°	54.3	4.6
70°-80°	21.6	1.8
80°-90°	4.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.5	58.0
0°-40°	888.9	74.9
0°-60°	1105.5	93.2
0°-90°	1186.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1186.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1151	
5°	1125	105
15°	971	271
25°	692	311
35°	312	201
45°	161	127
55°	100	90
65°	54	54
75°	20	22
85°	5	5
90°	0	



TEST NUMBER: P365368

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8030-F6LBXVM1-MW-BTR85

CANDELA DISTRIBUTION (FULL):

0°	
0°	1150.9
2.5°	1145.6
5°	1125.4
7.5°	1095.1
10°	1056.8
12.5°	1014.5
15°	970.8
17.5°	921.7
20°	859.8
22.5°	785.2
25°	691.8
27.5°	587.6
30°	479.3
32.5°	387.9
35°	311.9
37.5°	256.1
40°	214.5
42.5°	184.2
45°	160.7
47.5°	142.5
50°	127.1
52.5°	113.6
55°	100.2
57.5°	88.1
60°	76.0
62.5°	65.2
65°	54.5
67.5°	44.4
70°	35.6
72.5°	26.9
75°	19.5
77.5°	13.4
80°	8.7
82.5°	5.4
85°	4.7
87.5°	2.7
90°	0.0

(END OF REPORT)