

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364724

Luminaire Tested: **FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BTR89BV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364724  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BTR89BV  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR 0.125", 3000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2223.0 lumens  
Efficiency: N/A  
Efficacy: 82.3 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 27  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364724

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BTR89BV

### Luminous Intensity Polar Plot





TEST NUMBER: P364724

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BTR89BV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	249089
5°	243305
10°	223623
15°	199018
20°	168571
25°	134054
30°	94245
35°	39334
40°	13581
45°	3514
50°	1771
55°	1635
60°	1604
65°	1593
70°	1570
75°	2075
80°	2309
85°	3861



TEST NUMBER: P364724

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BTR89BV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	313.4	14.1
10°-20°	743.7	33.5
20°-30°	767.4	34.5
30°-40°	326.4	14.7
40°-50°	39.2	1.8
50°-60°	11.8	0.5
60°-70°	9.3	0.4
70°-80°	7.4	0.3
80°-90°	4.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1824.5	82.1
0°-40°	2150.9	96.8
0°-60°	2201.9	99.1
0°-90°	2223.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2223.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3479	
5°	3385	313
15°	2685	744
25°	1697	767
35°	450	326
45°	35	39
55°	13	12
65°	9	9
75°	8	7
85°	5	4
90°	0	



TEST NUMBER: P364724

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-LI-BTR89BV

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3478.8
2.5°	3456.3
5°	3385.1
7.5°	3261.3
10°	3075.7
12.5°	2892.9
15°	2684.8
17.5°	2450.5
20°	2212.3
22.5°	1963.9
25°	1696.8
27.5°	1421.2
30°	1139.9
32.5°	808.1
35°	450.0
37.5°	258.7
40°	145.3
42.5°	75.0
45°	34.7
47.5°	18.7
50°	15.9
52.5°	14.1
55°	13.1
57.5°	12.2
60°	11.2
62.5°	10.3
65°	9.4
67.5°	8.4
70°	7.5
72.5°	7.5
75°	7.5
77.5°	6.6
80°	5.6
82.5°	5.6
85°	4.7
87.5°	2.8
90°	0.0

(END OF REPORT)