

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364659

Luminaire Tested: **FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BL89AM**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364659
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-44)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BL89AM
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, OPAL SMOOTH 0.125", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 788.0 lumens
Efficiency: N/A
Efficacy: 38.8 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364659

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P364659

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	94	98	94	91		94	91	89		90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	75		82	78	74		79	75	72	70
3	90	80	71	65	88	78	70	64	75	68	63		72	67	62		70	65	61	59
4	82	70	62	55	80	69	61	54	67	59	54		64	58	53		62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	46		58	51	46		56	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41		52	45	40		51	45	40	38
7	65	51	42	36	63	50	42	36	49	41	36		47	41	36		46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32		43	37	32		42	36	32	30
9	56	43	35	29	55	42	34	29	41	34	29		40	33	29		39	33	29	27
10	53	40	32	26	52	39	31	26	38	31	26		37	31	26		36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7610
5°	7584
10°	7555
15°	7531
20°	7479
25°	7426
30°	7381
35°	7299
40°	7242
45°	7158
50°	7058
55°	6896
60°	6709
65°	6431
70°	5974
75°	5287
80°	4326
85°	2789



TEST NUMBER: P364659

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.3	3.3
10°-20°	75.1	9.5
20°-30°	113.7	14.4
30°-40°	137.1	17.4
40°-50°	142.8	18.1
50°-60°	129.6	16.4
60°-70°	98.1	12.5
70°-80°	53.4	6.8
80°-90°	11.8	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	215.1	27.3
0°-40°	352.2	44.7
0°-60°	624.7	79.3
0°-90°	788.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	788.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	279	
5°	277	26
15°	266	75
25°	246	114
35°	219	137
45°	185	143
55°	145	130
65°	100	98
75°	50	53
85°	9	12
90°	0	



TEST NUMBER: P364659

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	278.6
2.5°	277.9
5°	276.6
7.5°	275.2
10°	272.4
12.5°	269.7
15°	266.3
17.5°	262.2
20°	257.3
22.5°	252.5
25°	246.4
27.5°	240.9
30°	234.0
32.5°	227.2
35°	218.9
37.5°	210.7
40°	203.1
42.5°	194.2
45°	185.3
47.5°	175.7
50°	166.1
52.5°	155.8
55°	144.8
57.5°	134.5
60°	122.8
62.5°	111.2
65°	99.5
67.5°	87.2
70°	74.8
72.5°	63.1
75°	50.1
77.5°	38.4
80°	27.5
82.5°	17.2
85°	8.9
87.5°	3.4
90°	0.0

(END OF REPORT)