

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364670

Luminaire Tested: **FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BTR89BV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364670  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BTR89BV  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR 0.125", 2000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1627.0 lumens  
Efficiency: N/A  
Efficacy: 80.1 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364670

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BTR89BV

### Luminous Intensity Polar Plot





TEST NUMBER: P364670

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BTR89BV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	79
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	182305
5°	178071
10°	163669
15°	145661
20°	123378
25°	98107
30°	68979
35°	28784
40°	9936
45°	2572
50°	1303
55°	1198
60°	1174
65°	1169
70°	1151
75°	1522
80°	1691
85°	2793



TEST NUMBER: P364670

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BTR89BV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	229.4	14.1
10°-20°	544.3	33.5
20°-30°	561.7	34.5
30°-40°	238.9	14.7
40°-50°	28.7	1.8
50°-60°	8.7	0.5
60°-70°	6.8	0.4
70°-80°	5.4	0.3
80°-90°	3.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1335.3	82.1
0°-40°	1574.2	96.8
0°-60°	1611.6	99.1
0°-90°	1627.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1627.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2546	
5°	2478	229
15°	1965	544
25°	1242	562
35°	329	239
45°	25	29
55°	10	9
65°	7	7
75°	6	5
85°	3	3
90°	0	



TEST NUMBER: P364670

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-LI-BTR89BV

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2546.1
2.5°	2529.7
5°	2477.5
7.5°	2387.0
10°	2251.1
12.5°	2117.3
15°	1965.0
17.5°	1793.5
20°	1619.2
22.5°	1437.4
25°	1241.8
27.5°	1040.1
30°	834.3
32.5°	591.4
35°	329.3
37.5°	189.4
40°	106.3
42.5°	54.9
45°	25.4
47.5°	13.7
50°	11.7
52.5°	10.3
55°	9.6
57.5°	8.9
60°	8.2
62.5°	7.5
65°	6.9
67.5°	6.2
70°	5.5
72.5°	5.5
75°	5.5
77.5°	4.8
80°	4.1
82.5°	4.1
85°	3.4
87.5°	2.1
90°	0.0

(END OF REPORT)