

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366149

Luminaire Tested: **FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL84
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 3000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2458.0 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366149

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P366149

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58	66	61	58	65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86472
5°	86106
10°	81795
15°	74300
20°	64654
25°	54968
30°	43239
35°	24669
40°	11100
45°	4674
50°	1475
55°	448
60°	306
65°	246
70°	224
75°	296
80°	142
85°	282



TEST NUMBER: P366149

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.7	12.0
10°-20°	730.9	29.7
20°-30°	828.2	33.7
30°-40°	480.1	19.5
40°-50°	106.5	4.3
50°-60°	11.7	0.5
60°-70°	3.8	0.2
70°-80°	2.5	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1852.8	75.4
0°-40°	2332.9	94.9
0°-60°	2451.1	99.7
0°-90°	2458.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2458.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3166	
5°	3140	294
15°	2627	731
25°	1824	828
35°	740	480
45°	121	106
55°	9	12
65°	4	4
75°	3	2
85°	1	1
90°	0	



TEST NUMBER: P366149

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	3165.7
2.5°	3168.5
5°	3140.3
7.5°	3071.9
10°	2949.0
12.5°	2800.0
15°	2627.4
17.5°	2445.5
20°	2224.2
22.5°	2024.5
25°	1823.8
27.5°	1610.0
30°	1370.9
32.5°	1088.7
35°	739.8
37.5°	475.4
40°	311.3
42.5°	203.5
45°	121.0
47.5°	67.5
50°	34.7
52.5°	15.9
55°	9.4
57.5°	7.5
60°	5.6
62.5°	4.7
65°	3.8
67.5°	2.8
70°	2.8
72.5°	2.8
75°	2.8
77.5°	1.9
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)