

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366151

Luminaire Tested: **FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL86**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366151  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL86  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 3000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2418.0 lumens  
Efficiency: N/A  
Efficacy: 89.6 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 27  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366151

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL86

### Luminous Intensity Polar Plot





TEST NUMBER: P366151

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL86

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	85062
5°	84705
10°	80467
15°	73092
20°	63601
25°	54072
30°	42536
35°	24269
40°	10918
45°	4597
50°	1449
55°	438
60°	300
65°	239
70°	224
75°	296
80°	142
85°	282



TEST NUMBER: P366151

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL86

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	289.0	12.0
10°-20°	719.0	29.7
20°-30°	814.7	33.7
30°-40°	472.3	19.5
40°-50°	104.7	4.3
50°-60°	11.5	0.5
60°-70°	3.8	0.2
70°-80°	2.4	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1822.6	75.4
0°-40°	2294.9	94.9
0°-60°	2411.2	99.7
0°-90°	2418.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2418.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3114	
5°	3089	289
15°	2585	719
25°	1794	815
35°	728	472
45°	119	105
55°	9	11
65°	4	4
75°	3	2
85°	1	1
90°	0	



TEST NUMBER: P366151

CATALOG NUMBER: FLD6BX30D010-FEU6B35-8027-F6LBXVM1-WMH-BL86

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3114.1
2.5°	3116.9
5°	3089.2
7.5°	3021.9
10°	2901.1
12.5°	2754.4
15°	2584.7
17.5°	2405.7
20°	2188.0
22.5°	1991.5
25°	1794.1
27.5°	1583.8
30°	1348.6
32.5°	1070.9
35°	727.8
37.5°	467.7
40°	306.2
42.5°	200.2
45°	119.0
47.5°	66.4
50°	34.1
52.5°	15.7
55°	9.2
57.5°	7.4
60°	5.5
62.5°	4.6
65°	3.7
67.5°	2.8
70°	2.8
72.5°	2.8
75°	2.8
77.5°	1.8
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)