

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365391

Luminaire Tested: **FLD6BX20D010-FEU6B12-8035-F6LBXVM1-MW-BTR94**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-21)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-MW-BTR94
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM GLASS, TEMPERED CLEAR 0.187", 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1221.0 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365391

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-MW-BTR94

Luminous Intensity Polar Plot





TEST NUMBER: P365391

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-MW-BTR94

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	98	93	89	94	91	87	91	88	85	88	86	84	82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	72	69	68
5	87	78	71	66	85	77	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57
7	78	67	60	56	76	66	60	55	65	59	55	64	59	55	63	58	54	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	52	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86423
5°	84734
10°	80471
15°	75329
20°	68280
25°	56701
30°	40678
35°	27892
40°	20460
45°	16607
50°	14292
55°	12683
60°	11012
65°	9301
70°	7327
75°	5312
80°	3381
85°	3943



TEST NUMBER: P365391

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-MW-BTR94

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.2	9.0
10°-20°	283.3	23.2
20°-30°	321.6	26.3
30°-40°	205.9	16.9
40°-50°	128.6	10.5
50°-60°	91.1	7.5
60°-70°	54.5	4.5
70°-80°	21.2	1.7
80°-90°	4.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	715.1	58.6
0°-40°	921.0	75.4
0°-60°	1140.6	93.4
0°-90°	1221.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1221.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1207	
5°	1179	110
15°	1016	283
25°	718	322
35°	319	206
45°	164	129
55°	102	91
65°	55	54
75°	19	21
85°	5	5
90°	0	



TEST NUMBER: P365391

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-MW-BTR94

CANDELA DISTRIBUTION (FULL):

0°	
0°	1207.0
2.5°	1202.2
5°	1178.9
7.5°	1146.6
10°	1106.8
12.5°	1060.8
15°	1016.2
17.5°	960.6
20°	896.1
22.5°	812.4
25°	717.7
27.5°	603.2
30°	492.0
32.5°	395.2
35°	319.1
37.5°	262.1
40°	218.9
42.5°	186.6
45°	164.0
47.5°	144.8
50°	128.3
52.5°	115.3
55°	101.6
57.5°	88.5
60°	76.9
62.5°	65.2
65°	54.9
67.5°	44.6
70°	35.0
72.5°	26.8
75°	19.2
77.5°	13.0
80°	8.2
82.5°	5.5
85°	4.8
87.5°	2.7
90°	0.0

(END OF REPORT)