

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365392

Luminaire Tested: **FLD6BX20D010-FEU6B12-8035-F6LBXVM1-MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-5)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-MW
Description: VANDAL RESISTANT OPEN, MATTE WHITE REFLECTOR, 2000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1763.9 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.94
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 20.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365392

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-MW

Luminous Intensity Polar Plot





TEST NUMBER: P365392

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	98	93	88	102	96	91	87	93	89	85	89	86	83	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71
4	91	81	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	64	52	46	41	63	52	45	41	51	45	41	50	45	41	49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39555
5°	38703
10°	36615
15°	34347
20°	31955
25°	29334
30°	24857
35°	18670
40°	13397
45°	10021
50°	8078
55°	7167
60°	6512
65°	5966
70°	5463
75°	5003
80°	4452
85°	3667



TEST NUMBER: P365392

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.9	7.5
10°-20°	340.5	19.3
20°-30°	441.0	25.0
30°-40°	353.0	20.0
40°-50°	205.9	11.7
50°-60°	135.7	7.7
60°-70°	92.0	5.2
70°-80°	50.4	2.9
80°-90°	13.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	913.4	51.8
0°-40°	1266.5	71.8
0°-60°	1608.0	91.2
0°-90°	1763.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1763.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1448	
5°	1412	132
15°	1215	341
25°	973	441
35°	560	353
45°	259	206
55°	150	136
65°	92	92
75°	47	50
85°	12	14
90°	0	



TEST NUMBER: P365392

CATALOG NUMBER: FLD6BX20D010-FEU6B12-8035-F6LBXVM1-MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1448.1
2.5°	1438.9
5°	1411.5
7.5°	1372.4
10°	1320.1
12.5°	1271.3
15°	1214.6
17.5°	1155.5
20°	1099.3
22.5°	1040.7
25°	973.3
27.5°	889.7
30°	788.1
32.5°	678.1
35°	559.9
37.5°	460.7
40°	375.7
42.5°	311.2
45°	259.4
47.5°	219.9
50°	190.1
52.5°	167.6
55°	150.5
57.5°	134.8
60°	119.2
62.5°	105.5
65°	92.3
67.5°	80.6
70°	68.4
72.5°	57.7
75°	47.4
77.5°	37.6
80°	28.3
82.5°	19.5
85°	11.7
87.5°	4.4
90°	0.0

(END OF REPORT)